


CUSTOMER PRINT


PART NUMBER: W17980-XSG-P-300

- NOTES:
- 1. ALL PARTS TO BE BULK PACKED
  - 2. CONTACTS SHIPPED UNASSEMBLED
  - 3. ALL DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE


ASS'Y P/N	NO. OF CONTACTS	KEY STYLE
W17980-5SG-P-300	5 #26	A-KEY
W17980-6SG-P-300	6 #26	B-KEY
W17980-7SG-P-300	7 #26	A-KEY




**FACE VIEW**  
W17980-5SG-P-300  
5 POSITION  
A-KEY





HEX NUT  
MAT'L: UV PBT, BLACK  
GASKET  
MAT'L: NEOPRENE, BLACK




7/16-28 UNEF-2A  
MOD. THREAD  
PANEL CONNECTOR, FEMALE  
MAT'L: UV PBT, BLACK




.130±.015  
[3.3±0.4]  
CONTACT  
HEIGHT




(5-7) #26 SOCKET CONTACTS, CRIMP  
MAT'L: GOLD PLATED COPPER ALLOY




**WIRE VIEW**  
W17980-5SG-P-300




**FACE VIEW**  
W17980-6SG-P-300  
6 POSITION  
B-KEY




**WIRE VIEW**  
W17980-6SG-P-300



**RECCOMENDED  
PANEL CUT-OUT**




**FACE VIEW**  
W17980-7SG-P-300  
7 POSITION  
A-KEY



**WIRE VIEW**  
W17980-7SG-P-300

CUSTOMER APPROVAL			
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.			
APPROVED BY: _____			
DATE: _____			

A	MA	08-13-20	RELEASED PER PDR 18004-2	
	JGK	8/13/19	DRAWING CREATED FOR PDR #18004	
REV.	INIT.	DATE	DESCRIPTION	
	JGK	8/13/19	ORIG. DRAWN BY: JGK	 601 E. WILDWOOD VILLA PARK, IL 60181
			CHECKED BY:	
			APPROVED BY:	TITLE: PANEL MOUNT ASSEMBLY (5-7) #26 SOCKET CONTACTS, CRIMP INSTA-CLICK™ MICRO-CON-X STANDARD PRODUCT
			SCALE: NTS	CUSTOMER: W17980-XSG-P-300
			SIZE: B	PART NUMBER: W17980-XSG-P-300
			SHEET: 1 OF 1	REV: A
			FILE: W17980-XSG-P-300	
			DIRECTORY: SLW	

DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS UNLESS INDICATED

RoHS COMPLIANT

➤ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX