







REVISIONS					
#	LTN	DESCRIPTION	DATE	OWN	APP'D
AF5	REVISED	PER ECO-16-004800	12SEP2016	NK	MZ
AG	REVISED	PER ECO-17-004657	05APR2017	RS	MZ
AH	REVISED	PER ECO-19-014836	23OCT2019	RS	MZ
AJ	REVISED	PER ECO-20-011431	28AUG2020	SG	MZ



- CONNECTOR WILL ACCEPT POSTED TYPE III+ PIN CONTACTS.
- CONTACT BODY: SELECT GOLD OVER NICKEL.
CONTACT POST: TIN-LEAD PER MIL-T-10727 OVER COPPER PER MIL-C-14550A.
- RECOMMENDED PC BOARD HOLE SIZE FOR CONTACT POST: 1.02±.08[.040±.003] DIA.
- CONTACT BODY: SELECT GOLD OVER NICKEL.
CONTACT POST: TIN OVER NICKEL.
- POSITIONS LOADED WITH CONTACTS: 1-4, 10-17, 19-22, 24, 25, 29, 30, 32, 33.
- POSITIONS LOADED WITH CONTACTS: 1-20, 22-28, 30-37.
- OBsolete PARTS: OBsolete CIS STREAMLINING PER D.RENAUD/D.SINISI.
- CONTACT BODY: TIN OVER NICKEL.
CONTACT POST: TIN OVER NICKEL.
- CONTACT BODY: SELECT GOLD OVER NICKEL.
CONTACT POST: TIN/LEAD OVER NICKEL.
- CONTACT BODY: TIN/LEAD OVER NICKEL.
CONTACT POST: TIN/LEAD OVER NICKEL.

	△5	NO	YES	NO	—	.220	3-206934-0
OBsolete	△5	NO	YES	YES	—	.170	2-206934-9
OBsolete	△5	NO	YES	NO	—	.413	2-206934-8
PRELIMINARY	△5	NO	YES	NO	—	.257	2-206934-7
OBsolete	△9	NO	YES	YES	—	.119	2-206934-6
OBsolete	△5	NO	NO	NO	.150±.003	.240	2-206934-5
△10	△10	NO	NO	NO	.150±.003	.220	2-206934-3
OBsolete	△5	NO	NO	YES	.150±.003	.119	2-206934-2
OBsolete	△5	NO	NO	NO	.150±.003	.119	2-206934-1
△6	△5	NO	YES	YES	—	.618	2-206934-0
OBsolete	△5	NO	NO	NO	.150±.003	.618	1-206934-9
△5	△5	NO	NO	NO	.150±.003	.429	1-206934-8
△5	△5	NO	YES	YES	—	.119	1-206934-7
OBsolete	△10	NO	NO	YES	.150±.003	.429	1-206934-5
△10	△10	NO	YES	NO	—	.618	1-206934-4
△10	△10	NO	YES	NO	—	.220	1-206934-3
△6	△11	NO	NO	NO	.150±.003	.429	1-206934-2
△5	△5	NO	NO	NO	.150±.003	.220	1-206934-1
OBsolete	△10	YES	NO	YES	—	.119	1-206934-0
△10	△10	YES	YES	YES	—	.119	206934-9
OBsolete	△10	NO	NO	NO	.150±.003	.618	206934-7
△10	△10	NO	NO	NO	.150±.003	.429	206934-6
△10	△10	NO	NO	NO	.150±.003	.119	206934-5
OBsolete	△10	NO	YES	NO	—	.220	206934-4
△10	△10	NO	NO	NO	.158±.001	.618	206934-3
△10	△10	NO	NO	NO	.158±.001	.429	206934-2
△10	△10	NO	NO	NO	.150±.003	.220	206934-1
CONTACT FINISH	M3 INSERTS	4-40 INSERTS	PERIPHERAL SEAL	B	A	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: J.GALLUCCI 5-30-91	TE Connectivity	
DIMENSIONS: INCHES		CHK: W.GLENKER 4-14-92	NAME: K.BEAVER	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPRO: PRODUCT SPEC 108-10024	RECEPTACLE ASSEMBLY, POSTED, STD SEX, SERIES 1, 23-37, CPC	
MATERIAL: SEE CALLOUT		APPLICATION SPEC: —	SIZE: CAGE CODE: DRAWING NO: A1 00779	
CONTACT: △2		WEIGHT: —	RESTRICTED TO: —	
CUSTOMER DRAWING		SCALE: 2:1	SHEET 1 OF 1 REV AJ	