

Miniature Incandescent Indicators

FOR REAR MOUNTING IN 9/16" CLEARANCE HOLE

FOR 6 TO 60V OPERATION



T-2
WITH TELEPHONE
SLIDE BASE

See lamp ratings
on page J.

MATERIALS AND FINISHES

- **Mounting Bushing:** Standard—white nickel finish. Optional—black nickel finish.
- **Lens Holder:** Standard—polished chrome finish. Optional—white nickel, black nickel or satin chrome finish.
- **Standard Hardware:** Three (3) knurled rings—one brass, polished chrome finish; two rings brass, white nickel finish.
- **Optional Hardware:** One mounting nut—brass, white nickel finish. One knurled ring—brass, polished chrome finish. One internal-tooth lockwasher—steel, cadmium plated with yellow iridescent chromate finish.
- **Terminals:** Solder — brass, hot tinned. Screw—brass, white nickel finish.

NOTE: Where optional metal finish is chosen for lens holder, the same finish will be supplied for knurled ring (s).

How to designate the three digit part number suffix (—XXX)

Finish	Resistor	Hardware
1 — white nickel 2 — black nickel 3 — polished chrome	0 — none	5 — three knurled rings 6 — knurled ring, internal-tooth lockwasher, mtg. nut

NOTE: The part numbers listed on this page indicate standard indicator lights. The above table provides the standard and optional designations for Finish and Hardware.

17 SERIES
70 SERIES

BASE PART NUMBERS

WITH SCREW-ON LENS CAPS

solder terminals	screw terminals
70-0428-11-305	70-1328-11-305


CAP PART NUMBERS

COMPLETE ASSEMBLY PART NUMBERS

STOVEPIPE 17-0931-300 transparent 17-0951-300 translucent 17-0991-300 internal fluting	17-0428-0931-305 17-0428-0951-305 17-0428-0991-305	17-1328-0931-305 17-1328-0951-305 17-1328-0991-305
STOVEPIPE 70-1111-300 back frosted 70-1131-300 unfrosted 70-1191-300 internal fluting	70-0428-1111-305 70-0428-1131-305 70-0428-1191-305	70-1328-1111-305 70-1328-1131-305 70-1328-1191-305

Part numbers shown in gray are normally in inventory at your Dialight Distributor.

■ Specify translucent colors as follows: Red—0951, Green—0952, Yellow (amber)—0973, White—0975, Light Yellow—0976.



17-1328-0931-305

Stovepipe lens

70-0428-1191-305

Stovepipe lens

70-0428-1131-306

Stovepipe lens

Typical assembly with optional hardware