

BU-7020-B-XX-@

(Test Lead: Dual Stackable Banana Plug to Individual Stacking Banana Plugs)



- The BU-7020-B is a test lead with dual stackable, 4mm banana plug to individual stacking banana plugs. The dual stackable banana plug mates with any standard 4mm banana jacks and are spaced at the industry standard 0.75" (19mm).
- Constructed with RG58/U coaxial cable. Center conductor is 20 AWG (19x33) tinned copper and the shield is tinned copper braid (95% coverage).
- Material: Banana plugs Nickel-plated beryllium copper, brass
 Overmold Polypropylene
- Rating: Current 50 Ohms
 Voltage Hands-free testing to 300 VRMS
- Length: The "XX" in the part number represents the length in inches.
 Standard lengths: 12", 24", 36", 48"
- Color: The "@" in the part number represents over-mold color for one banana. Available colors: -0 Black, -2 Red