


HONEYWELL
PART NUMBER
83278

REV	DOCUMENT	CHANGED BY	CHECK
B	0069593	VKK 27SEP10	CMH

NOTES:

1. DUAL CIRCUIT PRESSURE SWITCH.
2. ADJUSTMENT RANGE 18-24 PSI.
3. SEE SPEC. 99005 FOR MANUFACTURING SPECIFICATION.

5. THE DATE CODE SHALL CONSIST OF FOUR DIGITS W/THE 1ST TWO DIGITS BEING THE YEAR AND THE 2ND TWO DIGITS BEING THE WEEK OF THE YEAR.



DESIGN UNITS: INCH			
TOLERANCES UNLESS NOTED:			
NO PLACES	X	±	-
ONE PLACE	.X	±	.020
TWO PLACE	.XX	±	.020
THREE PLACE	.XXX	±	.005
ANGLES	X	±	0° 30'
THIRD ANGLE PROJECTION			

DRAWN	KMJ	14OCT99
CHECK	-	-
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
AUTOCAD 2D		

Honeywell				
TITLE PRESSURE SWITCH D.C. METRI-PACK 5000 SERIES SWITCH				
SIZE	TYPE	CAGE CODE	DRAWING NAME	REV
B	E	-	83278	B
SCALE 2:1			SHEET	1 OF 1