


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	02JUL2015	DL	CW
	A1	ECR-18-019196	02JAN2019	WQR	CW
	B	ECR-20-014876	27JUL2021	WQR	CW



Technical drawing of the 1000 Series 2000mm long, showing front and side views. The front view (top) shows a rectangular unit with a central horizontal slot and two vertical slots on the sides. The side view (bottom) shows the unit's profile, including the top and bottom flanges and the central slot. Dimensions are indicated: 139.6 for the width and 96.8 for the height.

This diagram illustrates the exploded view of the 1000 Series LED Flood Light. It shows the main light body with a mounting bracket, the lens assembly, and the mounting hardware. The light body is designed for wall or pole mounting, featuring a robust bracket and a secure lens cover. The lens assembly is shown separately, highlighting the LED array and the protective lens. The mounting hardware includes a bracket, a mounting arm, and a mounting plate, all of which are shown in their relative positions for assembly.

注 释：

1. 技术参数：

主体材料： 铝合金




表面处理： 粉末喷涂， 灰色

防护等级： IP65（配合）

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 02JUL2015		TE Connectivity							
		CHK CHRIS WANG 02JUL2015									
		APVD XU XIANG 02JUL2015									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME H24B-SGR/SDR/SDRM/SGRH/SDRH/ SDRHM-LB-PG/M							
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±									
MATERIAL		FINISH									
-		-		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
-		-		A2		-		C-T16X0243XXXX00		-	
Customer Drawing				SCALE		1:2		SHEET		1 of 4	
								REV		B	

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET I	-	-	-






TYPE 4: H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,SIDE ENTRY 2M25,
BOTTOM ENTRY M20+PLASTIC PROTECTION COVER
OTHER SPEC REFER TO TYPE 2


类型4: H24B下壳,表面安装,彩锌单扣,侧出2M25,底出M20+带塑料保护盖
其余规范参考类型2

T1610243121-000	H24B-SGR-LB-PG21	H24B HOUSING,SURFACE MOUNTED, METAL SINGLE LOCKING,PG21,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,灰色粉末喷涂	PG21	-	TYPE 1 类 型 1	
T1610243125-000	H24B-SGR-LB-M25	H24B HOUSING,SURFACE MOUNTED, METAL SINGLE LOCKING,M25,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M25,灰色粉末喷涂	M25	-		
T1610243221-000	H24B-SGR-LB-2PG21	H24B HOUSING,SURFACE MOUNTED, METAL SINGLE LOCKING,2PG21,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,灰色粉末喷涂	PG21	PG21		
T1610243225-000	H24B-SGR-LB-2M25	H24B HOUSING,SURFACE MOUNTED, METAL SINGLE LOCKING,2M25,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M25,灰色粉末喷涂	M25	M25		
T1620243121-000	H24B-SDR-LB-PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG21, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,带塑料保护盖,灰色粉末喷涂	PG21	-	TYPE 2 类 型 2	
T1620243125-000	H24B-SDR-LB-M25	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,M25, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M25,带塑料保护盖,灰色粉末喷涂	M25	-		
T1620243221-000	H24B-SDR-LB-2PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG21, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,带塑料保护盖,灰色粉末喷涂	PG21	PG21		
T1620243225-000	H24B-SDR-LB-2M25	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2M25, PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M25,带塑料保护盖,灰色粉末喷涂	M25	M25		
T1620243421-000	H24B-SDRM-LB-PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING, PG21,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,带金属保护盖,灰色粉末喷涂	PG21	-	TYPE 3 类 型 3	
T1620243425-000	H24B-SDRM-LB-M25	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING, M25,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M25,带金属保护盖,灰色粉末喷涂	M25	-		
T1620243321-000	H24B-SDRM-LB-2PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING, 2PG21,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,带金属保护盖,灰色粉末喷涂	PG21	PG21		
T1620243325-000	H24B-SDRM-LB-2M25	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING, 2M25,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M25,带金属保护盖,灰色粉末喷涂	M25	M25		
T1620242520-000	H24B-SDR-LB-2M25/M20	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,SIDE ENTRY 2M25, BOTTOM ENTRY M20,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,侧出2M25,底出M20,带塑料保护盖,灰色粉末喷涂	M25	M25	TYPE 4 类 型 4	
PART NUMBER 料 号	DESCRIPTION 描 述			IG1	IG2	TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 02JUL2015 CHK DAVID LI 02JUL2015 CHRIS WANG APVD XU XIANG 02JUL2015		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±. 3 PLC ±. 4 PLC ±. ANGLES ±.		NAME H24B-SGR/SDR/SDRM/SGRH/SDRH/ SDRHM-LB-PG/M	
		PRODUCT SPEC 108-137013 APPLICATION SPEC 114-137013		SIZE A2	
MATERIAL - -		FINISH - -		CAGE CODE -	
		WEIGHT -		DRAWING NO C-T16X0243XXXX00	
		Customer Drawing		SCALE 1:2 SHEET 2 OF 4 REV B	

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 02JUL2015	 TE Connectivity			
DIMENSIONS:		CHK CHRIS WANG 02JUL2015				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD XU XIANG 02JUL2015	NAME H24B-SGR/SDR/SDRM/SGRH/SDRH/ SDRHM-LB-PG/M			
	0 PLC	±	PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO
	1 PLC	±	108-137013	A2	-	©-T16X0243XXXX00
	2 PLC	±	APPLICATION SPEC	SCALE	1:2	SHEET 3 OF 4
	3 PLC	±	114-137013	REV	B	
MATERIAL	FINISH	±	WEIGHT	Customer Drawing		
-	-	-	-			
-	-	-	-			

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-

T1650243121-000	H24B-SGRH-LB-PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG21,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,高结构,灰色粉末喷涂	PG21	-	TYPE 5 类 型 5
T1650243125-000	H24B-SGRH-LB-M25	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,M25,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M25,高结构,灰色粉末喷涂	M25	-	
T1650243129-000	H24B-SGRH-LB-PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG29,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG29,高结构,灰色粉末喷涂	PG29	-	
T1650243132-000	H24B-SGRH-LB-M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,M32,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M32,高结构,灰色粉末喷涂	M32	-	
T1650243221-000	H24B-SGRH-LB-2PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG21,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,高结构,灰色粉末喷涂	PG21	PG21	
T1650243229-000	H24B-SGRH-LB-2PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG29,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG29,高结构,灰色粉末喷涂	PG29	PG29	
T1650243232-000	H24B-SGRH-LB-2M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2M32,HIGH CONSTRUCTION,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M32,高结构,灰色粉末喷涂	M32	M32	TYPE 6 类 型 6
T1660243121-000	H24B-SDRH-LB-PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG21,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,高结构,带塑料保护盖,灰色粉末喷涂	PG21	-	
T1660243129-000	H24B-SDRH-LB-PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG29,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG29,高结构,带塑料保护盖,灰色粉末喷涂	PG29	-	
T1660243132-000	H24B-SDRH-LB-M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,M32,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M32,高结构,带塑料保护盖,灰色粉末喷涂	M32	-	
T1660243221-000	H24B-SDRH-LB-2PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG21,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,高结构,带塑料保护盖,灰色粉末喷涂	PG21	PG21	
T1660243229-000	H24B-SDRH-LB-2PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG29,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG29,高结构,带塑料保护盖,灰色粉末喷涂	PG29	PG29	
T1660243232-000	H24B-SDRH-LB-2M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2M32,HIGH CONSTRUCTION,PLASTIC PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M32,高结构,带塑料保护盖,灰色粉末喷涂	M32	M32	TYPE 7 类 型 7
T1660243121-100	H24B-SDRHM-LB-PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG21,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG21,高结构,带金属保护盖,灰色粉末喷涂	PG21	-	
T1660243129-100	H24B-SDRHM-LB-PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,PG29,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,PG29,高结构,带金属保护盖,灰色粉末喷涂	PG29	-	
T1660243132-100	H24B-SDRHM-LB-M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,M32,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,M32,高结构,带金属保护盖,灰色粉末喷涂	M32	-	
T1660243221-100	H24B-SDRHM-LB-2PG21	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG21,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG21,高结构,带金属保护盖,灰色粉末喷涂	PG21	PG21	
T1660243229-100	H24B-SDRHM-LB-2PG29	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2PG29,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2PG29,高结构,带金属保护盖,灰色粉末喷涂	PG29	PG29	
T1660243232-100	H24B-SDRHM-LB-2M32	H24B HOUSING,SURFACE MOUNTED,METAL SINGLE LOCKING,2M32,HIGH CONSTRUCTION,METAL PROTECTION COVER,POWDER COATED,GREY H24B下壳,表面安装,彩锌单扣,2M32,高结构,带金属保护盖,灰色粉末喷涂	M32	M32	
PART NUMBER 料 号	DESCRIPTION 描 述		IG1	IG2	TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -
-

DWN DAVID LI 02JUL2015
CHK CHRIS WANG 02JUL2015
APVD XU XIANG 02JUL2015
PRODUCT SPEC 108-137013
APPLICATION SPEC 114-137013
WEIGHT -
Customer Drawing

TE Connectivity

NAME
H24B-SGR/SDR/SDRM/SGRH/SDRH/
SDRHM-LB-PG/M

SIZE
A2

CAGE CODE
-

DRAWING NO
T16X0243XXXX00

RESTRICTED TO
-

SCALE
1:2

SHEET
4

OF
4

REV
B

1471-9 (3/13)