




- NOTES:
1. ALL PART TO BE BULK PACKED
 2. CONTACTS SUPPLIED UNASSEMBLED
 3. ALL DIMENSION ARE REFERENCE ONLY

**FACE VIEW**


P/N: 3280-4PG-5XX

**FACE VIEW**


P/N: 3280-5PG-5XX

**FACE VIEW**


P/N: 3280-6PG-5XX

**FACE VIEW**

P/N: 3280-7PG-5XX

**FACE VIEW**


P/N: 3280-8PG-5XX

**FACE VIEW**

P/N: 3280-9PG-5XX

B









ASS'Y P/N	COUPLING RING COLOR
3280-XPG-5XXCC1	WHITE
3280-XPG-5XXCC2	RED
3280-XPG-5XXCC3	BLUE
3280-XPG-5XXCC4	LIGHT GREY
3280-XPG-5XXCC5	YELLOW
3280-XPG-5XXCC6	MAROON
3280-XPG-5XXCC7	GREEN



B

CONTACT HEIGHTS

FOR CUSTOMER REFERENCE

O-RING
MAT'L: RUBBER,BLACKPIN CONNECTOR, MALE
MAT'L: NYLON, BLACK
NO. OF CONTACTS SEE CHART(4-9)-#20 PIN CONTACTS
MAT'L: GOLD PLATED
COPPER ALLOYCOUPLING RING
MAT'L: NYLON, BLACK
FOR 3280-XPG-5XXCCX
SEE COUPLING RING COLOR CHARTGROMMET
MAT'L: RUBBER, BLACK
FOR CABLE O.D.
SEE TABLESLEEVE
MAT'L: NYLON,BLACKBACKSHELL
MAT'L: NYLON,BLACK(2) #4 X 3/8
H-L SELF TAPPING SCREWS
MAT'L: STAINLESS STEELSTRAP
MAT'L: NYLON,BLACKGROMMET, DAISY CHAIN
MAT'L: RUBBER, BLACK
FOR 3280-XPG-5DCØ .375
[9.5]
TYP.

NO OF CONTACTS

B

CONN. KIT P/N	NO. OF CONTACTS	CONN. KIT P/N	GROMMET FOR CABLE	"X" DIM.
3280-4PG-5XX	4-#20	3280-XPG-5DC	SEE DAISY CHAIN	Ø 0.77 [19.6mm]
3280-5PG-5XX	5-#20	3280-XPG-515	.156 I.D. FOR CABLE .15-.17 O.D. [3.8-4.3mm]	Ø 0.77 [19.6mm]
3280-6PG-5XX	6-#20	3280-XPG-518	.187 I.D. FOR CABLE .18-.20 O.D. [4.6-5.1mm]	Ø 0.77 [19.6mm]
3280-7PG-5XX	7-#20	3280-XPG-521	.225 I.D. FOR CABLE .21-.23 O.D. [5.3-5.8mm]	Ø 0.77 [19.6mm]
3280-8PG-5XX	8-#20	3280-XPG-524	.250 I.D. FOR CABLE .24-.27 O.D. [6.1-6.8mm]	Ø 0.77 [19.6mm]
3280-9PG-5XX	9-#20	3280-XPG-528	.285 I.D. FOR CABLE .28-.29 O.D. [7.1-7.4mm]	Ø 0.77 [19.6mm]
		3280-XPG-530	.312 I.D. FOR CABLE .30-.32 O.D. [7.6-8.1mm]	Ø 0.77 [19.6mm]
		3280-XPG-535	.375 I.D. FOR CABLE .35-.40 O.D. [8.9-10.2mm]	Ø 0.83 [21.1mm]

B

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____

DATE: _____

RoHS COMPLIANT

B	AN	03-22-21	DRAWING NUMBER WAS 3280-XPG-5XX, ADDED COUPLING RING TABLE AND CONTACT HEIGHT VIEW, ADDED 3280-XPG-535, AND "X" DIM. TO CHART, UPDATED STRAP STYLE. PER ECR 9543
A	SS	01-14-19	DRAWING CREATED PER DOR 19-E149SL #1 SUPERSEDED DRAWING 3280-8PG-5XX
REV.	INIT.	DATE	DESCRIPTION
			ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.
			ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.
			ORIG. DRAWN BY: SS DATE: 01-14-19 CHECKED BY:
			APPROVED BY:
			SCALE: NTS SIZE: B SHEET: 1 OF 1
			FILE: 3280-XPG-5XX(CCX) DIRECTORY: SLW
			TITLE: CONNECTOR ASS'Y KIT (4-9) #20 PIN CONTACTS (CRIMP) MULTI-CON-X STANDARD PRODUCT
			CUSTOMER: 3280-XPG-5XX(CCX)
			REV B

DIMENSIONS IN BRACKETS [] ARE METRIC