


NOTE:

MATERIAL

HOUSING
FLANGE
CONTACT
SHELL
O-RING
SEALING COMPOUND
HARDWARE

PBT UL94V-0, BLACK
PBT UL94V-0, BLACK
BRASS, PLATING P/N KEY BELOW
STEEL, NICKEL
SILICONE
EPOXY
BRASS; NICKEL PLATED

ELECTRICAL

POWER CONTACT RATED CURRENT
VOLTAGE
INSULATOR RESISTANCE
POWER CONTACT RESISTANCE
WATER PROOF

P/N KEY BELOW
1000 VAC 1 MIN
5 GOhms MIN.
2.0 mOhms MAX.
IP67

ENVIRONMENT

OPERATION TEMPERATURE

-25°C TO +85°C

SERIES _____ CDFS3W3203LYYY
CDF = COMBO DSUB FLANGE
CONTACT TYPE _____
S = SOLDER CUP
POSITION _____
3W3
GENDER _____
2 = FEMALE
POWER CONTACT AMPERAGE _____
2 = 20 AMPS
4 = 40 AMPS
HARDWARE OPTIONS _____
1 = 4-40 THREADED INSERTS/4-40 JACKSCREWS
CONTACT PLATING OPTIONS _____
1 = GOLD FLASH
2 = 30u" GOLD PLATING

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

J. KADEL

DATE:

04/07/2020

TOLERANCES

X. ±0.40
.X ±0.30
.XX ±0.20
.XXX ±0.10

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:

NTS

SHEET

OF

1

1

REV

1

DWG NO.

CDFS3W3203LYYY