


CATALOG NUMBER	STRANDED COPPER CONDUCTOR SIZE (AWG)		NO. RIBS	DIMENSIONS - IN [mm]				COLOR CODE	WIRE STRIP LENGTH	INSTALLATION TOOLING PANDEUIT DIE PART NO. DISET COLOR & INDEX NO. NO. OF CRIMPS (I)		
	RUN	TAP		A	Q	T (MATL THICKNESS)	V			CT-2001	CT-1700**	CT-920, CT-920CH, CT-930, CT-930CH, CT-940CH*, CT-2940*
CTAPF10-16-C	14	16-14	0	.41 [10.4]	.13 [3.3]	.06 [1.5]	.19 [4.8]	RED [12.7]	CD-2001-8 RED P21 (1)			
	12	16-12										
CTAPF8-12-C	10	14	0	.67 [17.0]	.19 [4.8]	.07 [1.8]	.26 [6.6]	BLUE [17.5]	CD-2001-6 BLUE P24 (1)	BLUE P24 (2)		
	8	12										
CTAPF6-12-C	8	10-8	0	.67 [17.0]	.24 [6.1]	.07 [1.8]	.32 [8.1]	GRAY [17.5]	CD-2001-4 GRAY P29 (1)	GRAY P29 (2)		
	6	12-10										
CTAPF4-12-C	6	8-6	1	1.25 [31.8]	.28 [7.1]	.07 [1.8]	.40 [10.2]	BROWN [33.3]	CDM-2001-2 BROWN P33M (1)	BROWN P33 (4)	CDM-920-2 BROWN P33M (1)	
	5,4	12-8										
CTAPF3-12-C	5,4	6-5	1	1.25 [31.8]	.31 [7.9]	.08 [2.0]	.46 [11.7]	GREEN [33.3]	CDM-2001-1 GREEN P37M (1)	GREEN P37 (4)	CDM-920-1 GREEN P37M (1)	
	3	12-6										
CTAPF2-12-C	4	4	1	1.25 [31.8]	.33 [8.4]	.08 [2.0]	.51 [13.0]	PINK [33.3]	CD-2001-1/0 PINK P42 (1)		CDM-920-1/0 PINK P42M (1)	
	3	5										
CTAPF1-12-C	2	12-6	2	1.82 [46.2]	.40 [10.2]	.08 [2.0]	.57 [14.5]	BLACK [47.6]	CDM-2001-2/0 BLACK P45 (1)		CDM-920-2/0 BLACK P45M (1)	
	3	4-3										
CTAPF1/0-12-L	2	5-4	2	1.82 [46.2]	.42 [10.7]	.09 [2.3]	.63 [16.0]	ORANGE [47.6]	CD-2001-3/0 ORANGE P50 (1)		CDM-920-3/0 ORANGE P50M (1)	
	1	12-5										
CTAPF2/0-12-Q	1	4-3	2	1.82 [46.2]	.48 [12.2]	.09 [2.3]	.71 [18.0]	PURPLE [47.6]	CD-2001-4/0 PURPLE P54 (1)		CDM-920-4/0 PURPLE P54M (1)	
	1	2-1										
CTAPF3/0-12-Q	1/0	12-4	2	1.82 [46.2]	.55 [14.0]	.09 [2.3]	.81 [20.6]	YELLOW [47.6]	CD-2001-250 YELLOW P62 (3)		CDM-920-250 YELLOW P62M (1)	
	2/0	12-3										
CTAPF3/0-12-Q	1/0	1-1/0	2	1.82 [46.2]	.55 [14.0]	.09 [2.3]	.81 [20.6]	YELLOW [47.6]	CD-2001-250 YELLOW P62 (3)		CDM-920-250 YELLOW P62M (1)	
	2/0	2-1										
CTAPF3/0-12-Q	3/0	12-2	2	1.82 [46.2]	.55 [14.0]	.09 [2.3]	.81 [20.6]	YELLOW [47.6]	CD-2001-250 YELLOW P62 (3)		CDM-920-250 YELLOW P62M (1)	
	3/0	12-2										



****CT-1700 CRIMP DIE POCKETS ARE INTEGRATED INTO THE TOOL HEAD**



CERTIFIED LISTED

NOTES:

1. MATERIAL: COPPER
2. ULLISTED AND CSA CERTIFIED FOR APPLICATIONS UP TO 600 VOLTS. TEMPERATURE RATING 90 °C
3. PACKAGE QTY:
 - C = 100
 - L = 50
 - Q = 25

[illegible]

PANDUIT CORP. TINEY PARK, ILLINOIS

NON-INSULATED THIN-WALL C-TAP CONNECTORS CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED
DIMENSIONAL TOLERANCES ARE:
(.X) ± — (.XXX) ± —

BY	MAT'L:	SCALE	NOTE
----	--------	-------	------

SEE NOTES	DWG
DRAWING NO / CAD FILE	DWG

C41172 05