




P.C.B. LAYOUT



N = Number of poles

$$\text{Dim L} = (N-1) \times 3.5 + 2.90$$

$$\text{Dim P} = (N-1) \times 3.5$$

POLES	Dim L	Dim P
2p-6p	±0.15	±0.15
7p-12p	±0.2	±0.2
13p-18p	±0.3	±0.3
19p-24p	±0.4	±0.4

SIGN	DATE	DESCRIPTION	APPROVER
△			
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Terminal(housing): Thermoplastic (UL94V-0)
- Item ② Contact pin: Brass Tin plated

Electrical: cULus

- Voltage rating: 150V
- Current rating: 2A
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:
- Critical dimension: ③

OL xx 1 0 0 0 xxxx G

POLES
02 pole
''' '''
24 pole

G RoHS compliant
(lead<4%)
In copper Alloy
0000: Standard
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		OL-3.5mm series DIP (Match with NY 3.5)			
PART NO.	OLxx1000xxxxG			DWG NO.	80L0001
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Guoxue 2014.07.07	Guoxue 2014.07.07		Tolerance
					X. ±0.50
					X.X ±0.30
				UNIT: mm	X.XX ±0.10
				SCALE: NONE	X° ±1°
				SHEET: 01/01	REV.: B