



| SIGN                                           | DATE | DESCRIPTION | APPROVER |
|------------------------------------------------|------|-------------|----------|
| △                                              |      |             |          |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |      |             |          |





Material:

- Item ④ Terminal(housing): PA66 30% GF (UL94V-0)
- Item ⑤ Contact pin : copper Tin plated

Electrical:

- Voltage rating: 160V
- Current rating: 5.5A
- Withstanding Voltage: 1.32 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C ±10°C/5 Sec
- APPROVAL:

cULus



PCB Layout

K3 xx 1 1 x 0 xxxx G

No. OF POLES

06: 3x2 POLES

09: 3x3 POLES

:

:

72: 3x24 POLES

COLOR

0 Black (RAL9005)

3 Orange(RAL2011/P)

5 Green(RAL6018/T)

6 Blue (RAL5015/A)

8 Grey(RAL7035/D)

G: Pb<40000ppm

A000: "@" Logo (Standard)

△ A00A: "ANYTEK" Mark

Any special item by customer request. please contact sales department.

|      |       |       |       |       |       |       |       |       |       |       |       |       |
|------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| POLE |       | 3x2   | 3x3   | 3x4   | 3x5   | 3x6   | 3x7   | 3x8   | 3x9   | 3x10  | 3x11  | 3x12  |
| A    |       | 8.50  | 12.00 | 15.50 | 19.00 | 22.50 | 26.00 | 29.50 | 33.00 | 36.50 | 40.00 | 43.50 |
| B    |       | 3.50  | 7.00  | 10.50 | 14.00 | 17.50 | 21.00 | 24.50 | 28.00 | 31.50 | 35.00 | 38.50 |
| Tol. | ±0.15 |       |       |       |       |       | ±0.20 |       |       |       |       |       |
| POLE | 3x13  | 3x14  | 3x15  | 3x16  | 3x17  | 3x18  | 3x19  | 3x20  | 3x21  | 3x22  | 3x23  | 3x24  |
| A    | 47.00 | 50.50 | 54.00 | 57.50 | 61.00 | 64.50 | 68.00 | 71.50 | 75.00 | 78.50 | 82.00 | 85.50 |
| B    | 42.00 | 45.50 | 49.00 | 52.50 | 56.00 | 59.50 | 63.00 | 66.50 | 70.00 | 73.50 | 77.00 | 80.50 |
| Tol. | ±0.25 |       |       |       |       |       | ±0.30 |       |       |       |       |       |

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |                                                     |                      |                      |                                                                                                                                                                                                                                                        |          |         |  |  |  |           |            |        |
|----------|-----------------------------------------------------|----------------------|----------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|---------|--|--|--|-----------|------------|--------|
| TITLE    | K3 3.5mm W/O Flange Series (180°-Vertical) DIP type |                      |                      |                                                                                                                                                                                                                                                        |          |         |  |  |  |           |            |        |
| PART NO. | K3xx11x00000G                                       |                      |                      |                                                                                                                                                                                                                                                        | DWG NO.  | 8K30010 |  |  |  |           |            |        |
| APPROVED | CHECKED                                             | DESIGNED             | DRAWN                | CUST NO.                                                                                                                                                                                                                                               |          |         |  |  |  | Tolerance |            |        |
|          |                                                     | Runner<br>2010.09.18 | Runner<br>2010.06.28 | <div><div></div><div></div></div> <div>UNIT: mm</div> <div>SCALE: NONE</div> |          |         |  |  |  | X. ±0.50  | X.X ±0.30  |        |
|          |                                                     |                      |                      | SHEET: 01/01                                                                                                                                                                                                                                           | REV.: A2 |         |  |  |  |           | X.XX ±0.10 | X° ±1° |