



THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.  
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.  
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE  
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.  
JBX1INSFCC

FEMALE INSULATOR, CRIMP CONTACT



| CONTACT LAYOUT  | 02                         | 03      | 04      | 05      |
|-----------------|----------------------------|---------|---------|---------|
| FRONT SIDE VIEW |                            |         |         |         |
| REAR SIDE VIEW  |                            |         |         |         |
| CONTACT         |                            |         |         |         |
| ISO VIEW        |                            |         |         |         |
| CONTACT         | ØC                         | 1.3     | 1.3     | 0.9     |
|                 | ØF                         | 1.4     | 1.4     | 1.1     |
|                 | MAX. AWG                   | 18      | 18      | 20      |
|                 | MAX. CURRENT RATING (A)    | 15      | 15      | 10      |
|                 | CONTACT RESISTANCE (mΩ)    | 3       | 3       | 3.5     |
| INSULATOR       | NUMBER OF CAVITY           | 2       | 3       | 4       |
|                 | MAX. CURRENT RATING        | 15      | 12      | 9       |
|                 | TEST VOLTAGE (Vrms)        | 1600    | 1300    | 1400    |
|                 | WORKING VOLTAGE (Vdc/Vrms) | 760/530 | 600/420 | 900/630 |

| ORIGIN                                                                                                                                                                               | COUNTRY | JURISDICTION | CLASSIFICATION |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|--------------|----------------|
| X                                                                                                                                                                                    | FR      | Not listed   | N/A            |
|                                                                                                                                                                                      | US      | EAR          | ECCN =EAR99    |
| These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited |         |              |                |

|                                       |               |
|---------------------------------------|---------------|
| LINEAR MEASURE:                       |               |
| THIRD ANGLE PROJECTION                |               |
| TOLERANCES UNLESS OTHERWISE SPECIFIED |               |
| No. OF PLACES                         | mm [INCH]     |
| ONE PLACE                             | ±3 [±.1]      |
| TWO PLACES                            | ±0.5 [±.02]   |
| THREE PLACES                          | ±0.25 [±.010] |
| ANGLES ±1°                            |               |

CONTACT TYPE : F (FEMALE)  
CONTACT TERMINATION : C (CRIMP)

MATERIAL :  
CONTACT: CUPRO NICKEL  
CLIP: COPPER ALLOY  
INSULATOR: PEEK  
FINISH:  
CONTACTS: GOLD



|     |                        |              |             |
|-----|------------------------|--------------|-------------|
| B   | REVISED PER ECN 12286  | RSK 06-10-15 | EV 06-10-15 |
| A   | RELEASED PER ECN 12264 | SKV 03-10-15 | EV 03-10-15 |
| REV | DESCRIPTION            | BY DATE      | CHKD DATE   |

|                                                               |  |                 |  |          |                   |          |
|---------------------------------------------------------------|--|-----------------|--|----------|-------------------|----------|
| DRAWING TITLE                                                 |  |                 |  |          |                   |          |
| JBX, SIZE 1, FEMALE INSULATOR, CRIMP CONTACT                  |  |                 |  |          |                   |          |
| CAT NO.                                                       |  |                 |  |          |                   |          |
| JBX1INSFC                                                     |  |                 |  |          |                   |          |
| CAGE NO: 09922                                                |  | SIZE: B         |  | APPROVAL |                   |          |
| CUSTOMER                                                      |  | SOURIAU         |  |          | DRAWN: SKV        | 02-02-15 |
|                                                               |  |                 |  |          | CHKD : EV         | 02-02-15 |
|                                                               |  |                 |  |          | DSGN : EV         | 02-02-15 |
|                                                               |  |                 |  |          | MFG : DH          | 02-02-15 |
|                                                               |  |                 |  |          | QC : BB           | 02-02-15 |
| INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994. |  | WWW.SOURIAU.COM |  |          | DRAWING SCALE: NA |          |
|                                                               |  |                 |  |          | DRAWING NO. REV   |          |
|                                                               |  |                 |  |          | JBX1INSFCC B      |          |
|                                                               |  |                 |  |          | 1 OF 2            |          |

THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.  
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.  
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE  
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.  
JBX1INSFCC

| CONTACT LAYOUT             | 06                      | 07      | 08      |
|----------------------------|-------------------------|---------|---------|
| FRONT SIDE VIEW            |                         |         |         |
| REAR SIDE VIEW             |                         |         |         |
| CONTACT                    |                         |         |         |
| ISO VIEW                   |                         |         |         |
| CONTACT                    | ØC                      | 0.7     | 0.7     |
|                            | ØF                      | 0.85    | 0.85    |
|                            | MAX. AWG                | 22      | 22      |
|                            | MAX. CURRENT RATING (A) | 7       | 7       |
| INSULATOR                  | CONTACT RESISTANCE (mΩ) | 5       | 5       |
|                            | NUMBER OF CAVITY        | 6       | 7       |
|                            | MAX. CURRENT RATING     | 7       | 7       |
|                            | TEST VOLTAGE (Vrms)     | 1400    | 1400    |
| WORKING VOLTAGE (Vdc/Vrms) |                         | 660/460 | 600/420 |

| ORIGIN                                                                                                                                                                               | COUNTRY | JURISDICTION | CLASSIFICATION |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|--------------|----------------|
| X                                                                                                                                                                                    | FR      | Not listed   | N/A            |
|                                                                                                                                                                                      | US      | EAR          | ECCN =EAR99    |
| These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited |         |              |                |

|                                       |               |
|---------------------------------------|---------------|
| LINEAR MEASURE:                       |               |
| THIRD ANGLE PROJECTION                |               |
| TOLERANCES UNLESS OTHERWISE SPECIFIED |               |
| No. OF PLACES                         | mm [INCH]     |
| ONE PLACE                             | ±3 [±.1]      |
| TWO PLACES                            | ±0.5 [±.02]   |
| THREE PLACES                          | ±0.25 [±.010] |
| ANGLES±1°                             |               |

|                                                               |  |                 |  |          |                   |          |
|---------------------------------------------------------------|--|-----------------|--|----------|-------------------|----------|
| DRAWING TITLE                                                 |  |                 |  |          |                   |          |
| JBX, SIZE 1, FEMALE INSULATOR, CRIMP CONTACT                  |  |                 |  |          |                   |          |
| CAT NO.                                                       |  |                 |  |          |                   |          |
| JBX1INSFC                                                     |  |                 |  |          |                   |          |
| CAGE NO: 09922                                                |  | SIZE: B         |  | APPROVAL |                   |          |
| CUSTOMER                                                      |  | SOURIAU         |  |          | DRAWN: SKV        | 02-02-15 |
|                                                               |  |                 |  |          | CHKD : EV         | 02-02-15 |
|                                                               |  |                 |  |          | DSGN : EV         | 02-02-15 |
|                                                               |  |                 |  |          | MFG : DH          | 02-02-15 |
|                                                               |  |                 |  |          | QC : BB           | 02-02-15 |
| INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994. |  | WWW.SOURIAU.COM |  |          | DRAWING SCALE: NA |          |
|                                                               |  |                 |  |          | DRAWING NO. REV   |          |
|                                                               |  |                 |  |          | JBX1INSFCC B      |          |
|                                                               |  |                 |  | 2 OF 2   |                   |          |

B

A