






PANDUIT P/N	WEIGHT	SPLIT SLEEVE TYPE
CMDSLC**	.10 lbs/10 Pcs [44.7 g/10 Pcs]	PHOS BRONZE
CMDSAQLC**		
CMDSLCZ**	.10 lbs/10 Pcs [44.4 g/10 Pcs]	ZIRCONIA
CMDSAQLCZ**		

NOTES:


1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR OF MODULE BASE, AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. MATERIALS:
 - a. MODULE BASE: ABS
 - b. ADAPTER HOUSING: PLASTIC
 - c. SPLIT SLEEVE: SEE TABLE
 - d. DUST CAP: PLASTIC
4. COMPATIBLE WITH TIA/EIA-604-10 (FOCIS-10) AND TIA/EIA-568B.3
5. DIMENSIONS IN BRACKETS ARE METRIC [mm]



MINI-COM LC SENIOR/SENIOR
DUPLEX FIBER OPTIC ADAPTER MODULE
CUSTOMER DRAWING



PANDUIT™
CORP.
TINLEY PARK, ILL 60477

THIRD ANGLE
PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES,
UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX) ± .010 (0.3)
(.XX) ± .03 (0.8) ANGLES

DRAWING FILENAME
M00948AJ_DC_00B.prntSCALE
NONEDRAWN BY
MC

REVIEW DRAWING NUMBERS

PART NO.
SEE TABLEDATE
06-26-03

SEE NOTES

DRAWING NO.
00948-17SIZE
A

1 03-11-05 MC RELEASED TO PRODUCTION

00948-17

REV DATE BY CHK DESCRIPTION

ECN - R CUST SUP OTH