

SUMMARY

Wires

Low voltage 3



Image is for illustrative purpose only

Series	2P
Termination type	Female solder
IP rating	50
AWG wire size	24.00 - 16.00
Cable Ø	0.00 - 0.00 mm
Status	active
Matching parts	CAB.M03.NLA.C52N

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model	CL*: Fixed receptacle, nut fixing
Keying	3 keys (alpha=0, gamma=60; Plug: male contacts; Receptacle: female contacts)
Housing Material	PSU (Polysulfone), black
Weight	6.48 g

Performance

Configuration	2P.M03 : 3 Low V.
Insulator	L: PEEK for solder contacts
Rated Current	17 Amps

Specifications


Contact Type: Solder
Contact Dia.: 1.6 mm (0.062in)
Bucket Dia.: 1.4 mm (0.055in)
Test voltage (kV rms) Contact-contact: 2.4
Air clearance min.: 1.5 mm
Creepage distance min.: 1.5 mm

Others

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Endurance (Shell): >1000 mating cycles
Temp (min / max): -50°C / +150°C
F ret (min): 150 N
F ret (max): 250 N
Steam sterilization: 20 times

DRAWINGS



Dimensions

	N	a
mm.	23.8	3.4-4.9
in.	0,94	0,13

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.