








DIM		TOL		
		1P--6P	7P--12P	13P--16P
Dim P	(N-1)×7.5	±0.15	±0.25	±0.35
Dim L	N×7.5+1.8	±0.15	±0.25	±0.35

N=NUMBER OF POLES



SIGN	DATE	DESCRIPTION	APPROVER
△	09/15'11	The color is changed from RAL7035/D to RAL7004/P	Runner
△	09/15'11	The dimension is changed from 2.1 to 2.2	Runner
△	09/15'11	The Material is changed	Runner
△	09/15'11	The tolerance is changed	Runner
△	09/25'13	change the dimension from 18.6&2.6 to 19.2&3.2	Da cheng
△	09/25'13	change the electrical specification	Da cheng

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ① Terminal body: Thermoplastic (UL94V-0)
- Item ② Terminal side body: Thermoplastic (UL94V-0)
- Item ③ Terminal cover: Thermoplastic (UL94V-0)

- Item ④ Contact pin : Copper, Tin Plated.
- Item ⑤ Spring clamp : Stainless steel
- Item ⑥ Contact pin : Copper, Tin Plated.

Electrical: cULus

- Voltage rating: 300 V
- Current rating(Sol): 30 A
- Current rating(Str): 35 A
- Solid wire(AWG): 10-24
- Stranded wire(AWG): 8-24
- Wire strip length: 15-16 mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +120°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus
- Critical dimension: ▽

RoHS compliant (lead<4%)
In copper Alloy

End Stackable

01: 1 POLES
02: 2 POLES
16: 16 POLES

Body Color

0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7004/P)
9 White(RAL1102)
C Multiple colors

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by customer request.
please contact sales department.

ANYTEK				CUSTOMER COPY	
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD					
TITLE	NK 7.5mm Series Vertical (Single tail B type)(第1P左端子靠边)			DWG NO.	8NK0002
PART NO.	NKxxA0x1xxxxG			CUST NO.	
APPROVED	CHECKED	DESIGNED	DRAWN	Tolerance	
		Da cheng	Da cheng	X. ±0.50	
		2013.09.25	2013.09.25	X.X ±0.30	
				X.XX ±0.10	
				X° ±1°	
				SHEET: 01/01	REV.: C