







SIZE	Part Num.	Threading	Headscrew	Packaging
09	8655MHRA0901LF	UNC 4.40	Black	BULK (see note 1)
	8655MHRA0901KLF	UNC 4.40	Black	KIT (see note 2)
	8655MHRA0902LF	M3	Grey	BULK
	8655MHRA0902KLF	M3	Grey	KIT





SIZE	Part Num.	Threading	Headscrew	Packaging
15	8655MHRA1501LF	UNC 4.40	Black	BULK (see note 1)
	8655MHRA1501KLF	UNC 4.40	Black	KIT (see note 2)
	8655MHRA1502LF	M3	Grey	BULK
	8655MHRA1502KLF	M3	Grey	KIT



SIZE	Part Num.	Threading	Headscrew	Packaging
37	8655MHRA3701LF	UNC 4.40	Black	BULK (see note 1)
	8655MHRA3701KLF	UNC 4.40	Black	KIT (see note 2)
	8655MHRA3702LF	M3	Grey	BULK
	8655MHRA3702KLF	M3	Grey	KIT



SIZE	Part Num.	Threading	Headscrew	Packaging
50	8655MHRA5001LF	UNC 4.40	Black	BULK (see note 1)
	8655MHRA5001KLF	UNC 4.40	Black	KIT (see note 2)
	8655MHRA5002LF	M3	Grey	BULK
	8655MHRA5002KLF	M3	Grey	KIT




www.fciconnect.com			surface ISO 1302	✓	tolerance std ISO 406	ISO 1101	projection ⊕	mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED				size A3	Scale 1:1
Dr	BART.S	2005/10/15	ANGULAR	LINEAR	0.X	±/		
Eng	LENOIR.M	2005/10/15			0.XX	±/		
Chr	LEGARE.P	2005/10/15	0° ±/°		0.XXX	±/	ECN	F11-0073
Appr	LEGARE.P	2005/10/15	Product family				Spec ref	
FCI			D-SUB METAL SHELLS				dwg no	10061512C
			ANGLED					Rev. J
			catalog no				CUSTOMER	sheet 2 of 3


REV C - 2006-03-28

CABLING INSTRUCTIONS


1- Use two halves of strain relief, different sizes can be mixed (Ø4,5,7 or 9)




2- Strip cable 18mm and shape to two pigtails




3- Attach the strain relief around the cable




4- Bend cable shielding back on outside of strain relief



5- Mount connector and cable into the backshell



6- Assemble the other half screwing force: 100 Ncm



Copyright FCI.

www.fciconnect.com			Surface ISO 1302		✓	tolerance std ISO 406 ISO 1101		projection 	mm 
			TOLERANCES UNLESS OTHERWISE SPECIFIED						
Dr	BART.S	2005/10/15	ANGULAR	LINEAR	0.X	±/	size	Scale	
Eng	LENOIR.M	2005/10/15			0.XX	±/	A3	3:2	
Chr	LEGARE.P	2005/10/15			0° ±/°	0.XXX	±/	ECN	F11-0073
Appr	LEGARE.P	2005/10/15	Product family D-Sub				Spec ref		
	title D-SUB METAL SHELLS					dwg no 10061512C		Rev J	
	ANGLED								
	catalog no					CUSTOMER		sheet 3 of 3	

REV E - 2006-03-28

PDM: Rev:J

STATUS:Released

Printed: Aug 20, 2011