

CT3130

Banana Plug Test Lead Set

Pair, Black & Red, 4mm Straight, Banana Plug to Right-Angle...

Description

Test lead pair, Black and Red. Most common lead for handheld DMMs. Right-Angle Banana Plug for the meter and straight banana plug for the probe or clip. With PVC jacketed wire, 1.00 mm² (17 AWG), length 100 cm (40").



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

Datasheet



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

IEC Rating	1,000 V CAT III / 600 V CAT IV
Current, Max	20 A
Resistance, Max	25 milliohms
Jacket Material	PVC
Length	100 cm (40")
Conductor Area	1.00 mm²
Wire Gauge	17 AWG
Stranding (# x dia.)	259 x 0.07
OD, mm (in)	3.8 mm (0.150")
Temperature (degrees)	-20 to +80C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com