



F.O. single connectors with glass fibres

Identification	Part No.	Drawing	Dimensions in mm
F.O. connectors for GI-fibre 50-62.5/125 μm F-SMA type for cable $\varnothing$ 2.8 mm F-ST type for cable $\varnothing$ 2.8 mm	 20 10 125 1212 20 10 125 2212	F-SMA type F-ST type 	 The ferrule of the FO connector for GI-fibre is ceramic Insertion loss: F-SMA GI/SI < 1.0 dB F-ST GI/SI < 0.5 dB
Coupling sleeve F-SMA type	 20 80 000 1071		F-SMA connector and coupling sleeve acc. to IEC 874-2
F-ST type	 20 80 000 1021		F-ST connector and coupling sleeve acc. to IEC 874-10 CECC 86123-801

¹⁾ HCS® = Hard Clad Silica is registered trademark of SpecTran Corporation