




1. UL LISTED AND CSA CERTIFIED FOR:
A. SOLID OR STRANDED COPPER WIRE

3. SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

5. INSTALLATION TOOLS:

A. UL LISTED AND CSA CERTIFIED: CT-100, CT-200
B. PANDUIT APPROVED: CT-260

6. WIRE STRIP LENGTH: $5/16^{+1/32}_{-0}$ (7.9 $^{+.8}_{-0}$)
 $7/16^{+1/32}_{-0}$ (11.1 $^{+.8}_{-0}$) FOR PS12



LISTED
587H
E52164



CERTIFIED
LR31212

								PANDUIT CORP. TINLEY PARK, ILLINOIS					
								NON-INSULATED PARALLEL SPLICE					
06	5/11	SB		Added Note #3									
REV	DATE	BY	CHK	DESCRIPTION			ECN #	CUST	PM	DRAWN BY	CHK'D	SCALE	DRAWING NO.
										DRL		NONE	A41339