





KU xx C 1 x 1 xxxx G
 No. OF POLES ————
 02: 2 POLES
 :
 :
 10: 10 POLES
 COLOR ————
 0: BLACK
 5: GREEN (RAL 6018/T)
 6: BLUE
 8: GREY (RAL 7035/D)

G: Pb<40000ppm
 0000: "@" Logo (Standard)
 000A: "ANYTEK" Mark
 Any special item by
 customer request.
 please contact sales
 department.

ANYTEK				CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE		KU 15.0mm Body Series (Right angle) with flange 2P-10P					
PART NO.		KUxxC1x1xxxxG		DWG NO.		8KU0003	
APPROVED		CHECKED		DESIGNED		DRAWN	
				CUST NO.			
		Runner 2011.04.25		Runner 2010.05.24			
				SHEET: 01/01		Tolerance X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°	
				UNIT: mm SCALE: NONE REV: R			