







REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C190347	2019/03/06	Vicky	Change Note



Recommended Panel
Cut-Out



7 PIN



6 PIN


Pin Assignments Front View

ADC-XXPMMS-SS7001


02: 2Pin

07: 7Pin

With Liquid Glue




Connector 1
2 Gasket
3 Nut




Note:


- * Important Dimension To Check.
- * Waterproof Rate: IP67, Unmated.
- * Housing: Thermoplastic, Black.
- * Pin: Copper Alloy, Gold Plated.
- * Nut: Thermoplastic, Black.
- * Gasket: Rubber, Gray.
- * Use with waterproof cap or dust cap
Maximum Panel Thickness: 1.8mm
- * Use without waterproof cap or dust cap
Maximum Panel Thickness: 3.0mm
- * Gasket and Nut are packed separately
in PE bags. (Gasket/Nut不組裝, 散裝出貨)




5 PIN



4 PIN




3 PIN



2 PIN

Pin Assignments Front View

UNIT: mm



TITLE
LARGE
PANEL SCREW M CONN M PIN

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE

TOLERANCE
.X ±0.25
.XX ±0.1
.XXX ±0.05
ANGLES ±1°

SCALE	SIZE	SHEET	OF
REV.	WC-REV.	QC	Inspection item

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.