





- Elevated socket strips are available in 5 different standoff heights:
- 416...006 uses pin # 0153-1
- 416...003 uses pin # 0153-2
- 416...007 uses pin # 0153-3
- 416...008 uses pin # 0153-4
- 416...001 uses pin # 0153-5
- See page 138 for details.
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 218 for details.
- Insulators are high temp. thermoplastic.



Ordering Information

Fig. 1

Series 416...006 Standoff Height = 5,99

416-XX-2_ -41-006000

Specify # of pins → 02-64

Fig. 2

Series 416...003 Standoff Height = 8,0

416-XX-2_ -41-003000

Specify # of pins → 02-64

Fig. 3

Series 416...007 Standoff Height = 10,21

416-XX-2_ -41-007000

Specify # of pins → 02-64

Fig. 4

Series 416...008 Standoff Height = 11,99

416-XX-2_ -41-008000

Specify # of pins → 02-64

Fig. 5

Series 416...001 Standoff Height = 15,09

416-XX-2_ -41-001000

Specify # of pins → 02-64

For Electrical,
Mechanical & Environmental
Data, See pg. 4

XX=Plating Code
See Below

For RoHS compliance
select ◇ plating code.

SPECIFY PLATING CODE XX=		93		43◇
Sleeve (Pin)		5,08µm Sn/Pb		5,08µm Sn
Contact (Clip)		0,76µm Au		0,76µm Au