



 OBSOLETE

1-3. MECHANICAL:

- 1-3-1. CONTACT RETENTION FORCE: 3 KG/CM (MIN).
- 1-3-2. OPERATING TEMPERATURE: -55°C TO +105°C.
- 1-3-3. SOLDERABILITY: 95% COVERAGE (MIN)
TEST TEMPERATURE= 230°C±10°C
TEST TIME= 3SEC ± 0.5SEC.



	38.5	44.00	20.00(.787)	4	2-1776489-7
	7.00	12.50	120.00(4.724)	24	2-1776489-4
△ ₃	7.00	12.50	115.00(4.528)	23	2-1776489-3
△ ₃	7.00	12.50	110.00(4.331)	22	2-1776489-2
△ ₃	7.00	12.50	105.00(4.134)	21	2-1776489-1
△ ₃	7.00	12.50	100.00(3.937)	20	2-1776489-0
△ ₃	7.00	12.50	95.00(3.740)	19	1-1776489-9
△ ₃	7.00	12.50	90.00(3.543)	18	1-1776489-8
△ ₃	7.00	12.50	85.00(3.346)	17	1-1776489-7
△ ₃	7.00	12.50	80.00(3.150)	16	1-1776489-6
△ ₃	7.00	12.50	75.00(2.953)	15	1-1776489-5
△ ₃	7.00	12.50	70.00(2.756)	14	1-1776489-4
△ ₃	7.00	12.50	65.00(2.559)	13	1-1776489-3
△ ₃	7.00	12.50	60.0(2.362)	12	1-1776489-2
△ ₃	7.00	12.50	55.00(2.165)	11	1-1776489-1
△ ₃	7.00	12.50	50.00(1.969)	10	1-1776489-0
△ ₃	7.00	12.50	45.00(1.772)	9	1776489-9
△ ₃	7.00	12.50	40.00(1.575)	8	1776489-8
△ ₃	7.00	12.50	35.00(1.378)	7	1776489-7
	7.00	12.50	30.00(1.181)	6	1776489-6
△ ₃	7.00	12.50	25.00(.984)	5	1776489-5
	7.00	12.50	20.00(.787)	4	1776489-4
	7.00	12.50	15.00(.591)	3	1776489-3
	7.00	12.50	10.00(.394)	2	1776489-2
	DIM C	DIM B	DIM A	NO. OF POSN	PART NUMBER



RECOMMENDED PC BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL		5/2/05		 TE Connectivity	
		CHK C RICHARD		5/2/05			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C RICHARD		NAME	
		0 PLC ± -		PRODUCT SPEC		HEADER, STRAIGHT, UNSHROUDED	
		1 PLC ± 0.3		—		5.0MM PITCH	
		2 PLC ± 0.25		APPLICATION SPEC		—	
		3 PLC ± -		—		SIZE	
		4 PLC ± -		—		CAGE CODE	
		ANGLES ± -		WEIGHT		DRAWING NO	
MATERIAL		FINISH		A2		00779	
-		-		CUSTOMER DRAWING		C-1776489	
						SCALE 5:1	
						SHEET 1 of 1	
						REV A1	