

NOTE:

MATERIAL

HOUSING: PBT UL94V-0, BLACK
CONTACT: BRASS
NUT: BRASS
SHELL: BRASS
O-RING: EPDM

FINISH



CONTACT: GOLD PLATED
OVER 50 μ NICKEL
NUT: NICKEL PLATED
SHELL: NICKEL PLATED

ELECTRICAL

RATED CURRENT: 4A
RATED VOLTAGE: 60V
INSULATION RESISTANCE: 100 M Ω hms MIN.
CONTACT RESISTANCE: 10 m Ω hms MAX.
WATER PROOF: IP67

ENVIRONMENT

OPERATION TEMPERATURE: -40°C TO +85°C
MAX WIRE AWG: 22



3 = BRASS/NICKEL (B/N) SHELL & NUT
S = STAINLESS STEEL (SS) SHELL & NUT
T = B/N SHELL / SS NUT

1 = GOLD FLASH
4 = 10 μ GOLD

858-005-203RLSY

RoHS COMPLIANT

UNITS = INCHES [MM]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: M. SIGMON DATE: 03-07-16

NorComp

SCALE: NTS SHEET 1 OF 1 REV 3

DWG NO. 858-005-203RLSY