

BU-7070-B-XX-@

(Test Lead: Dual Stackable Banana Plugs Each End, RG-58/U)



- Mueller's BU-7070-B is a test lead with dual, stackable 4mm banana plugs on each end. Banana plugs are spaced at 0.75" (19mm) and mate with any standard 4mm banana jacks.
- Constructed with RG-58/U coaxial cable. Center conductor is 20 AWG (19x33) tinned copper and the shield is tinned copper braid (95% coverage).
- Material: Banana plugs Nickel-plated phosphor bronze
 Overmold Polypropylene
- Rating: Impedance 50 Ohms
 Voltage Hands-free testing to 500 VRMS
- Length: The "XX" in the part number represents length in inches.
 Standard lengths: 24", 36", 48", 96"
- Color: The "@" in the part number represents the color of the overmold material on the banana plugs.
 Available colors: -0 Black, -2 Red
- RoHS 3 compliant