

INTERCONNECTS

SERIES 410, 411, 415 • 2,54 GRID SOLDER TAIL • DOUBLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3




FIG. 4

- Series 41X double row strip sockets are on 2,54 grid
- Various solder tails available: standard length, long for multi-layer boards, very low and ultra low profile. See Mill-Max #1001, #0134, #0501 or #1534 pins. See pages 161, 162 and 165 for details
- Hi-Rel, 4-finger BeCu #12 and #30 contact are rated at 3 amps. See pages 252 and 253 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 410...001		Standard Solder Tail						
	Specify number of pins		410-XX-2-41-001000 04-64						
FIG. 2	Series 411...001		Long Solder Tail						
	Specify number of pins		411-XX-2-41-001000 04-64						
FIG. 3	Series 415...001		Very Low Profile						
	Specify number of pins		415-XX-2-41-001000 04-64						
FIG. 4	Series 415...003		Ultra Low Profile						
	Specify number of pins		415-XX-2-41-003000 04-64						
RoHS - 2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Enviromental Data, See page 264									
SPECIFY PLATING CODE XX=			11	13	91	93	41	43	
Sleeve (Pin)			0,25µm Au	0,25µm Au	5,08µm Sn/Pb	5,08µm Sn/Pb	5,08µm Sn	5,08µm Sn	
Contact (Clip)			0,25µm Au	0,76µm Au	0,25µm Au	0,76µm Au	0,25µm Au	0,76µm Au	