

1234567

△ Dimension

DIM L	(N-1)×7.62+5.7
DIM A	(N-1)×7.62+5.0
DIM B	(N-1)×7.62

N=Number of poles

POLES	Tolerance
2p-6p	±0.15
7p-12p	±0.20
13p-16p	±0.30

SIGN	DATE	DESCRIPTION	APPROVER
△	11/21'09	The normal grey No. changed from RAL7004/P to RAL7035/D	Kind
△	03/03'10	Add the glue on the top	Wellch
△	03/03'10	The wire strip length is changed from 7~8mm to 8~9mm	Wellch
△	04/06'10	Add the 2P mark	RUNNER
△	02/21'13	add the safety certification icon or update the drawing	Da cheng
THIS IS CAD DRAWING, DO NOT REVISE MANUALL Y!!!			

Material

- Item 1 Terminal body:Thermoplastic (UL94V-0)
- Item 2 Terminal body:Thermoplastic (UL94V-0)
- Item 3 Terminal lever:Thermoplastic (UL94V-0) Orange(RAL2011/P)
- Item 4 Wire guard:Stainless Steel
- Item 5 Female contact:PhBz (CuSn) Tin plated

△ Electrical

cULus

- Voltage rating: 300V
- Current rating: 10A
- Solid wire(AWG): 12-26
- Stranded wire(AWG): 12-26
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40℃ to +115℃
- Safety Approval: 
- Critical dimension: 

HW xx 00 x 0 xxxx G


△ RoHS compliant
(lead<4%)
In copper Alloy






No. OF POLES	△ Body Color	0000 Standard @ Logo
02 2 POLES	0 Black (RAL9005)	000A Standard ANY Logo
03 3 POLES	2 Red (RAL3001/D)	Any special item by
... ..	3 Orange(RAL2011/P)	customer request,
16 16 POLES	4 Yellow(RAL1018/A)	please contact sales
	5 Green(RAL6018/T)	department.
	6 Blue (RAL5015/A)	
	△ 8 Grey(RAL7035/D)	
	C Green(RAL6018/U)	

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HW 7.62 Series Contact on down side				
PART NO.		HWxx00x0xxxxG		DWG NO.	8HW0503	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
						X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
		Da cheng 2013.02.21	Da cheng 2013.02.21		UNIT: mm SCALE: NONE REV.: F	
		SHEET: 01/01				



2P mark

E

D

C

B

A

E

D

C

B

A