

2




1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
NKBNCM**Y	.36 LB/10 PCS (165 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
 - 1- MODULE BASE
 - 1- BNC COUPLER (ASSEMBLED TO MODULE BASE)



PART NUMBER		PRODUCT SPEC/PKG SPEC	
NKBNCM**Y		N/A	
I.T. NUMBER		WORK INSTRUCTION	
N/A		N/A	
TITLE			
NETKEY 50ohm BNC COUPLER MODULE			
CUSTOMER DRAWING			
ITEM REVISION NAME		PANDUIT TM	
M02479HU/00.PRT			
DATASET FILE NAME		MATERIAL :	
M02479HU_DC205/00B.PRT			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		ABS	
.x ± .1 (2.54) .xxx ± .010 (.254) .xx ± .02 (.50) ANGLES : 5 °			
		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		02479-205	
DRAWN BY	DATE	CHK	SCALE
JSP	4-24-06		NONE
SHT 1 OF 1		SIZE	
		A	

2

1

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	10-5-12	BJN	MBVE	MBVE	A. LENGTH DIMENSION WAS 1.28	02479-205
R	4-24-06	JSP			RELEASED TO PRODUCTION	02479-205