




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/23/18	



SPECIFICATIONS:

Material:
 Housing: Nylon 46, rated UL 94V-0, Color: Black
 Contacts: Brass, 10u" min. Gold
 Shell A: Zinc Alloy, Nickel plated
 Shell B: Brass, Nickel plated
 Shell C: Brass, Nickel plated
 O-ring A: EPDM, Color: Black
 O-ring B: NBR, Color: Black
 Spring: Stainless
 Screw: Alloy Steel
 SR: TPR
 Environmental:
 Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710
APPROVALS DRAWN HR 11/23/18 CHECKED AC 11/23/18 APPROVED			TITLE WATERPROOF CONNECTOR, MALE M8 DIN, ASSEMBLY, SCREW TYPE, SOLDER		
SIZE X			PART NO. SD-PNLXX-MMTAL-S00-000		REV. -
REF: S00200T			SCALE: NTS		SHEET 1 OF 1