







POLE		2	3	4	5	6	7	8
A		13.24	20.86	28.48	36.10	43.72	51.34	58.96
B		7.62	15.24	22.86	30.48	38.10	45.72	53.34
Tol.		± 0.15			± 0.20			
POLE	9	10	11	12	13	14	15	16
A	66.58	74.20	81.82	89.44	97.06	104.68	112.30	119.92
B	60.96	68.58	76.20	83.82	91.44	99.06	106.68	114.30
Tol.		± 0.30			± 0.40			

SIGN	DATE	DESCRIPTION	APPROVER
△	12/02'08	Flange screw changed from "-" to "+/-"	Tony
△	3/11'09	Dim.A & Dim.B Changed	Tony
△	2009.12.18	Add UL standard	Jacke
△	2010.03.23	Add the 2p mark	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ③ Clamp: Steel Zinc plated
- Item ④ Terminal(Up body): Thermoplastic (UL94V-0)
- Item ⑤ Terminal(Down body): Thermoplastic (UL94V-0)
- Item ⑥ Female contact: PbBz(CuSn),Tin plated.
- Item ⑦ Terminal screw: Steel Zinc plating "- " slot type
- Item ⑧ Clampcage:Steel/steel Zinc plated
- Item ⑨ With flange screw: Steel Zinc plated, M2.5

Electrical: cULus

- Voltage rating: 300V
- Current rating: 20A
- Wire range:
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque: 3.5 Lb.-In.
- Screw: M2.5
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: 

VM xx 0 5 x 3 xxxx G

POLES

02: 02 pole

/// ///

16: 16 pole

Color

- 0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

— G: Pb<40000ppm

— 0000: “@” Logo (Standard)
(Steel screw plating Cr³⁺)

000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK				CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE		VM 7.62 mm W/ Flange Series					
PART NO.		VMxx05x3xxxxG		DWG NO.		8VM0501	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
			Jacke 2010.03.23	Jacke 2009.12.18			X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
					UNIT: mm SCALE: NONE		
					SHEET: 01/01		REV.: F