PART NO.	Packing reel	QTY
20279-001E-01	Corrugated paper reel	2500
20279-001E-02	Plastic reel	2500
20279-001E-03	Plastic reel	5000











RECOMMENDED FOOTPRINT PATTERN

MATING

Plug P/N 20278-***R-**
20351-***R-37



Plug P/N 20311-***R-**



Notes.

1. Material
 (1) Housing : LCP, UL94V-0, white
 (2) Contact : brass
  Au 0.1 μm MIN. over Ni 1.27 μm MIN.
 (3) Ground Contact : phosphor bronze
  Au 0.05 μm MIN. over Ni 1.27 μm MIN.
2. Coplanarity : 0.1mm MAX.
3. Packing : emboss tape
4. Mating partner Part No. :
  20278-***R-**
  20351-***R-37
  20311-***R-**
5. This is "Pb-free" connector.
6. RoHS compliant. DC0-7.2GHz

Notes.

1. 材料
 (1) ﾊｳｼﾞﾝｸﾞ : LCP, UL94V-0, 白色
 (2) ｺﾝﾀｸﾄ : 黄銅
  金ﾒｯｷ 0.1 μm MIN. 下地 ﾆｯｹﾙﾒｯｷ 1.27 μm MIN.
 (3) ｸﾞﾗﾝﾄﾞｺﾝﾀｸﾄ : りん青銅
  金ﾒｯｷ 0.05 μm MIN. 下地 ﾆｯｹﾙﾒｯｷ 1.27 μm MIN.
2. ｺﾌﾟﾗﾅﾘﾃｨ : 0.1mm MAX.
3. 梱包 : ｴﾝﾎﾞｽﾃｰﾌﾟ
4. 嵌合相手 Part No. :
  20278-***R-**
  20351-***R-37
  20311-***R-**
5. 本ｺﾈｸﾀは"Pb-free"である
6. RoHS指令を満足している

GENERAL TOLERANCE	
6 MAX.	±0.2
6 OVER MAX. 30	±0.3
30 OVER MAX. 120	±0.5
ANGLE	±2°

REV	ECN	BY	DATE	APP
i4	Z12046	H.M	Jan./20/'12	EK
13	Z10262	H.M	Jun./08/'11	E.K
12	Z11032	Y.H	Jan/28/'11	E.K
11	Z11030	H.M	Jan./26/'11	E.K
10	Z10101	Y.H	Mar./08/'10	E.K

REV.RECORD
SERIES No. R7

DESIGN'D BY	DATE
K.Ohbayashi	Jun./07/'01
CHK'D BY	DATE
E.Kawabe	Jun./07/'01
APP'D BY	DATE
K.Katabuchi	Jun./07/'01

CUSTOMER COPY

PROJECTION

DAI-ICHI SEIKO CO.,LTD.
I-PEX Business Company

TITLE: MHF series micro coaxial connector receptacle vertical

SCALE	UNIT	DWG. No.	SHEET	REV.
10:1	mm	20279	1/1	14

FORM REV.4

I-PEX Confidential III C

WAS T