




SPECIFICATIONS :

MATERIAL:

- 1.HOUSING MATERIAL: GLASS FILLED PBT(UL94V-0). Colour: Gray
- 2.CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{MM}$.
- 3.PLATING: GOLDFLASH PLATING AND NICKEL PLATING

OVERALL

ELECTRICAL:


- 1.VOLTAGE RATING: 125Vac RMS .
- 2.CURRENT RATING: 1.5AMP .
- 3.CONTACT RESISTANCE: $30\text{m}\Omega$ MAX .
- 4.INSULATION RESISTANCE: $500\text{M}\Omega$ MIN .
- 5.DIELECTRIC WITHSTANDING VOLTAGE: 1000V

MECHANICAL:

- 1.DURRABILITY : 750 CYCLES MIN.
- 2.INSETION FORCE: 2.2Kgf MAX.
- 3.RETENTION STRENGTH : 7.7Kgf MIN

ENVIRONMENTAL:

- 1.STORAGE TEMPRATURE : -40°C TO 85°C .
- 2.OPERATION TEMPRATURE : -40°C TO 70°C .



PCB LAYOUT
PCB THICKNESS: 1.6mm



GENERAL TOLERANCE		制 图 DRAWING	04	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD				
DIM	TOL	审 核 CHECK						
X.X	±0.30	批 准 APPROVAL		产 品 名 称 TITLE	网 络 插 座 (16H 全塑无灯)	版 本 REV.	A	
X.XX	±0.20	比 例 SCALE		产 品 料 号 PART NO.	HC-RJ45-5JB-1-6	单 位 UNITS	mm	
X.XXX	±0.10	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1	
Angle	±3.0°							