







RoHS 2.0

Kinghelm®



3D View



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A0.	/	新版发行	20.04.03	
A1.	/	重新核对图面	21.01.07	

PIN数	A±0.1	B±0.1	C±0.1
2P	7.60	4.50	1.25
3P	8.85	5.75	2.50
4P	10.10	7.00	3.75
5P	11.35	8.25	5.00
6P	12.60	9.50	6.25

Specifications:

- 1.Rated Voltage : 125V AC/DC
- 2.Rated Current : 1A AC,DC
- 3.Withstand Voltage : 200V AC/minute
- 4.Contact Resistance : 50mΩ(MAX.)
- 5.Insulation Resistance : 100MΩ(MIN.)
- 6.Storage Temperature Range:-40°C~+85°C;
- 7.Operation Temperature Range:-25°C~+70°C

C	插片	黄铜H65	镀镍锡	
B	插针	黄铜H65	镀镍锡	
A	基座	LCP	本色	
序号	品名	材质	电镀/颜色	备注

深圳市金航标电子有限公司			www.kinghelm.com.cn	
KH-A1251WF-05A			0755-28190160	
UNLESS OTHERWISE, GENERAL TOLERANCE: X. xxx ±0.05 X. xx ±0.15 X. x ±0.25 ANGULAR: X. xx° ±1° X. x° ±3° X. ° ±5°		NAME: 针座1.25卧贴5P无缺口		P/N: 09.09.01.004
		THIRD ANGLE PROJECTION 		DWG NO:
DRAWN:		UNIT: MM	SCALE: 1:1	SIZE: A4
CHECKED:		SHEET: 1/1	SHEET: 1/1	REV. A1
APPROVED:				