




REVISIONS


REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		
A1	/		独立各PIN数图纸, 增加开孔定位尺寸	2024.12.05	桑 莎



PART NO.:

X05 62 F X X X X

- ① Series No.
- ② Pin No.:62PIN;
- ③ Welding Board Angle :F-Female
- ④ T: Traditional C: Car-pin
- ⑤ Planting Category:
1:1U 2:2U 3:3U 4:4U 5:5U 6:6U 7:7U
- ⑥ Color:B-BLACK W-White BL-Blue
- ⑦ 1:TYPE-1; 2:TYPE-2; 5:TYPE-5; 7:TYPE-7



Specifications:

规格:


- 1.Voltage rating:250VAC/DC
额定电压: 250V AC/DC
- 2.Current rating:3A(T) / 5A(C) AC/DC
额定电流: 3A(冲针) / 5A(车针) AC/DC
- 3.Withstanding voltage:500V AC/minute
耐受电压: ≥500V AC/分钟
- 4.Temperature range: -55°C~+105°C
温度范围: -55°C~+105°C

- 5.Insulation resistance:1000MΩMIN
绝缘电阻: ≥1000MΩ
- 6.Contact resistance:30mΩMax
接触电阻: ≥30mΩ

Material:

- 7.Rubber core:PBT UL94V-0
胶芯: PBT UL94V-0
- 8.Terminal:Copper alloys
端子: 铜合金。
- 9.The iron shell:SPCC Nivkel Plating/
Tin Plating/Gold Plating
铁壳: SPCC,镀镍/镀锡/镀金

B、成品不能有弯针, R角不一致等不良。



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	桑 莎	VIEW:	D-SUB
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

XKB INDUSTRIAL PRECISION CO., LIMITED

SCALE PAGE REVISION
N/A 1/1 A1