








RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE




Part No	Pin	A	B	C
FPC1.0-WFX11-2P211-H20	2	1.00	3.10	6.90
FPC1.0-WFX11-3P211-H20	3	2.00	4.10	7.90
FPC1.0-WFX11-4P211-H20	4	3.00	5.10	8.90
FPC1.0-WFX11-5P211-H20	5	4.00	6.10	9.90
FPC1.0-WFX11-6P211-H20	6	5.00	7.10	10.90
FPC1.0-WFX11-7P211-H20	7	6.00	8.10	11.90
FPC1.0-WFX11-8P211-H20	8	7.00	9.10	12.90
FPC1.0-WFX11-9P211-H20	9	8.00	10.10	13.90
FPC1.0-WFX11-10P211-H20	10	9.00	11.10	14.90
.....	....	...	.....	.....
FPC1.0-WFX11-32P211-H20	32	(32-1)*1.0	(32+1)*1.0+0.10	(32+6)*1.0-0.10



序号	品名	材质
1	0.5 前翻胶芯 (H2.0)	LCP UL94V-0 本色
2	0.5 前翻端子 (H2.0)	铜合金 / 表面镀锡
3	0.5 前翻后盖 (H2.0)	LCP UL94V-0 黑色
4	0.5 前翻焊片 (H2.0)	铜合金 / 表面镀锡

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25° C ~ 85° C.
3. 额定电压: 50V, AC/DC (等效).
4. 接触电阻: ≤ 0.03 Ω.
5. 绝缘电阻: ≥ 500M Ω



GENERAL TOLERANCES UNLESS SPECIFIED		 <b>深圳市华明通电子有限公司</b> Shenzhen Huamingtong Electronics Co., Ltd	
.X ±0.30	.X° ±5°	PART NO.	TITLE:
.XX ±0.20	.XX° ±2°	FPC1.0-WFX11-NP211-H20	1.0 Pitch 前翻卧式下接 (H=2.0)
.XXX ±0.05	.XXX° ±1°	DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	SIZE A4
		APPD: Sophia	UNITS MM
			SCALE N:A
			SHEET 1/1