










Part No	Pin	A	B	C	D
FPC0. 5-WSX11-4P211-H20	4	1. 50	2. 56	7. 60	5. 20
FPC0. 5-WSX11-5P211-H20	5	2. 00	3. 06	8. 10	
FPC0. 5-WSX11-6P211-H20	6	2. 50	3. 56	8. 60	
FPC0. 5-WSX11-7P211-H20	7	3. 00	4. 06	9. 10	
FPC0. 5-WSX11-8P211-H20	8	3. 50	4. 56	9. 60	
FPC0. 5-WSX11-9P211-H20	9	4. 00	5. 06	10. 10	
FPC0. 5-WSX11-10P211-H20	10	4. 50	5. 56	10. 60	
FPC0. 5-WSX11-11P211-H20	11	5. 00	6. 06	11. 10	
FPC0. 5-WSX11-12P211-H20	12	5. 50	6. 56	11. 60	5. 75
.....					
FPC0. 5-WSX11-34P211-H20	34	16. 50	17. 56	22. 60	
FPC0. 5-WSX11-35P211-H20	35	17. 00	18. 06	23. 10	
FPC0. 5-WSX11-36P211-H20	36	17. 50	18. 56	23. 60	
.....					
FPC0. 5-WSX11-60P211-H20	60	(60-1)*0. 5	(60+1)*0. 5+0. 06	(60+11)*0. 5+0. 1	




序号	品名	材质
1	0.5 拉拔胶芯 (H2. 0)	LCP UL94V-0 本色
2	0.5 拉拔下接端子 (H2. 0)	铜合金 / 表面镀锡
3	0.5 拉拔卧式后盖 (H2. 0)	LCP UL94V-0 黑色
4	0.5 拉拔焊片 (H2. 0)	铜合金 / 表面镀锡

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
3. 额定电压: 50V, AC/DC.
4. 接触电阻: $\leq 0.03\Omega$.
5. 绝缘电阻: $\geq 500M\Omega$

适用扁平线 (Applicable Flat Cable)

适用线路板 (PCB LAYOUT)

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd				
.X ±0.30	.X° ±5°	PART NO. FPC0.5-WSX11-NP211-H20		TITLE: 0.5 Pitch H2.0 ZIF R/A Type 3 Unper CONN.		
.XX ±0.20	.XX° ±2°					
.XXX ±0.05	.XXX° ±1°	DESIGN: James		CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen			A4	MM
		APPD: Sophia			SCALE	SHEET
					N:A	1/1