




7		8	
REV.	REVISION DESCRIPTION	DATE	APPD

A





B

C

D

E

F



PCB LAYOUT

NOTES:

1. Rated voltage: 250V AC/DC
2. Rated current: 3A AC DC
3. Contact resistance: $\leq 20 \text{ m}\Omega$
4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
5. Withstand voltage: 800V AC/minute
6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
7. Material : PBT/PA6T
8. Pin Materials : Brass/Gold-Plated.

A

B

C


D

E

F

Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	B			A	B
1	TJC8-2.54-1AWT	/	2.54	9	TJC8-2.54-9AWT	20.32	22.86
2	TJC8-2.54-2AWT	2.54	5.08	10	TJC8-2.54-10AWT	22.86	25.40
3	TJC8-2.54-3AWT	5.08	7.62	11	TJC8-2.54-11AWT	25.40	27.94
4	TJC8-2.54-4AWT	7.62	10.16	12	TJC8-2.54-12AWT	27.94	30.48
5	TJC8-2.54-5AWT	10.16	12.70	~	~	~	~
6	TJC8-2.54-6AWT	12.70	15.24	20	TJC8-2.54-20AWT	48.26	50.80
7	TJC8-2.54-7AWT	15.24	17.78	~	~	~	~
8	TJC8-2.54-8AWT	17.78	20.32	42	TJC8-2.54-42AWT	104.14	106.68

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: DL25402-AWT (TJC8-2.54-AWT)	TITLE: 2.54 mm Pitch Wire To Board Wafer
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$	DR: Yuan Jun Rong	DATE: 21/08/01
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE: 21/08/01
FINISH:		APPD: Ren An De	DATE: 21/08/01
DRAWING NO:			



REV.	REVISION DESCRIPTION	DATE	APPD
B	新模优化	2020.5.5	Wu

NOTES:

Rated voltage: 250V AC/DC

Rated current: 3A AC DC

Contact resistance: $\leq 20 \text{ m}\Omega$

Insulation resistance: $\geq 1000 \text{ M}\Omega$





Withstand voltage: 800V AC/minute

Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$


Wire range: AWG#28~#22

Materials:


Terminal: Brass, Tin plated



SECTION A-A



SECTION B-B



SECTION C-C

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	$X^{\circ} : \pm 3.0^{\circ}$	PRODUCT NAME: DL25402-T (TJC8-2.54-T)	TITLE: 2.54 mm Pitch Wire To Board Crimp Terminal
.XX: ± 0.15	$.X^{\circ} : \pm 2.0^{\circ}$	DR: Yuan Jun Rong	DATE: 21/08/01
.XXX: ± 0.01	$.XX^{\circ} : \pm 1.0^{\circ}$	CHKD: Wu Hui	DATE: 21/08/01
FINISH:		APPD: Ren An De	DATE: 21/08/01
DRAWING NO:		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: B