



RoHS



Contacts	Dimensions		Contacts	Dimensions	
	A	B		A	B
2*1	2.54	0	2*21	53.34	50.80
2*2	5.08	2.54	2*22	55.88	53.34
2*3	7.62	5.08	2*23	58.42	55.88
2*4	10.16	7.62	2*24	60.96	58.42
2*5	12.70	10.16	2*25	63.50	60.96
2*6	15.24	12.70	2*26	66.04	63.50
2*7	17.78	15.24	2*27	68.58	66.04
2*8	20.32	17.78	2*28	71.12	68.58
2*9	22.86	20.32	2*29	73.66	71.12
2*10	25.40	22.86	2*30	76.20	73.66
2*11	27.94	25.40	2*31	78.74	76.20
2*12	30.48	27.94	2*32	81.28	78.74
2*13	33.02	30.48	2*33	83.82	81.28
2*14	35.56	33.02	2*34	86.36	83.82
2*15	38.10	35.56	2*35	88.90	86.36
2*16	40.64	38.10	2*36	91.44	88.90
2*17	43.18	40.64	2*37	93.98	91.44
2*18	45.72	43.18	2*38	96.52	93.98
2*19	48.26	45.72	2*39	99.06	96.52
2*20	50.80	48.26	2*40	101.6	99.06

材质

1. 塑胶: PA6T 黑色
2. 端子: 黄铜 镀金

深圳市富港科技有限公司									
图 视 									
2. 54排针弯针				PZ2. 54-2*nPW					
图样标记	重量	比例							
设计	Y X Y	日期	18. 12. 03	标准化	审定	日期			
校对	L P J	日期	18. 12. 03			日期			
工艺		日期							
审核	L Z W	日期	18. 12. 03						
PCB LAYOUT									
2. 54 									
)                									
发 放 部 门									
行 政 部									
业 务 部									
采 购 部									
工 程 部									
品 保 部									
生 产 部									