





REV.	ECN NO.	DATE	SIGN	DESCRIPTION

ALTW


CONFIDENTIAL

2014-10-24


R&D DEPT.



- Note:
- * $\varnothing$ Important Dimension To Check.
 - * Waterproof Rate: IP68
 - * Working Voltage Rating: AC 300 V
 - * Working Current Rating: 5A
 - * Flame Class: UL94V-0 (UV Resistance)
 - * Housing: Nylon+GF, Black
 - * Male Pin: Copper Alloy, Gold Plated
 - * Nut: Nylon+GF, Black
 - * Gasket: Silicone, Gary
 - * Use Without Waterproof Cap
Panel Thickness Max: 4.0mm
 - * Use With Waterproof Cap
Panel Thickness Max: 3.0mm



Pin Assignments
Front View



Recommended Panel Cut-out

UNIT:mm	TITLE X Lok B-Size Receptacle Front Fastened M Conn M 7 Pin			Amphenol LTW		ITEM NO BD-07PMMS-QC8001	DRAWN BY Micky	DATE 2014-10-24
	TOLERANCE .X ±0.25			安費諾亮泰企業股份有限公司		DWG NO BD-07PMMS-QC8001	CHECKED BY Spring	DATE 2014-10-24
	SCALE 2:1			REV. A		CUSTOMER ALTW	APPROVED BY Kevin	DATE 2014-10-24
	SIZE A4			SHEET 1 OF 1		8 FMW10702-01-02A1		