






THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Recommended Panel
Cut-Out



Pin Assignments
Front View



- Note:
- * (QC) Important Dimension To Check.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black.
 - * Male Pin: Copper Alloy, Gold Plated
 - * Gasket: Silicone, Gray
 - * Screw Nut: Nylon+GF, Black
 - * Use with waterproof cap or dust cap
Maximum Panel Thickness: 1.8mm
 - * Use without waterproof cap or dust cap
Maximum Panel Thickness: 3.0mm

UNIT:mm		TOLERANCE		TITLE		ITEM NO		DRAWN BY		DATE	
.X ±0.25		.XX ±0.1		LARGE		ADD-I8PMMS-SC700I		Jinhai		2015-07-17	
.XXX ±0.05		ANGLES ±1°		PANEL SCREW 18PIN M CONN M PIN		DWG NO		CHECKED BY		DATE	
SCALE 2:1		SIZE A4		SHEET 1 OF 1		ADD-I8PMMS-SC700I		Rensong		2015-07-17	
REV. A		WC-REV. A.1		(QC): Inspection item		CUSTOMER		APPROVED BY		DATE	
						ALTW		Jerry		2015-07-17	

Amphenol LTW
安費諾亮泰企業股份有限公司