


THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION2014

© COPYRIGHT 2010 BY TE CONNECTIVITYALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	25.JUN.'10	YH	HG
	B	REVISED (ECR-11-025149)	13.DEC.'11	YH	HG
	C	REVISED (ECR-14-016716)	11.NOV.'14	JM	HG



SCALE 1:1




NOTE.
1.MATING CONN'R ASSY P/N: 2005475
2.APPLICATION TEST SPEC:
MS210-12(EXT-2)(EXCEPT 4.4)

PURPLE	PA66-GF30	RETAINER HSG	2005471-6
COLOR	MATERIAL	DESCRIPTION	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm


3rd ANGLE PROJECTION

MATERIAL

SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0. PLC
1. PLC
2. PLC
3. PLC
4. PLC
ANGLES
± DECIMALS: ±0.5
± ANGLES: ±3°
±

FINISH

-

DWN
JM JEON
CHK
JW JUNG
APVD
HG CHO
PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

TE Connectivity

NAME

MCON 1.2mm RETAINER HSG
FOR ECU 91P PLUG ASS'Y

SIZE
A3

CAGE CODE
00779

DRAWING NO
C=2005471

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE 2:1

SHEET 1 OF 1

REV C

1470-19 (3/13)