


△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



製品番号		STUD SIZE	Hφ	INSULATION DIA	
製品番号		スタッドサイズ	Hφ	被覆外径 D	
171508	-1	#6	3.68	2.03~3.18	
	-2	#8	4.34	2.03~3.18	
	-3	#10	5	2.03~3.18	OBSOLETE (F)
	-4	#6	3.68	2.67~3.56	
	-5	#8	4.34	2.67~3.56	
	-6	#10	5	2.67~3.56	OBSOLETE (E)
	-7	5mm	5.26	2.03~3.18	OBSOLETE (1)
	-8	5mm (G)	5.2	2.67~3.56	
171508	-9	#4	3.02	2.03~3.18	OBSOLETE (H)

J					REVISED PER ECR-17-007066	T.G	N.Y	26MAY17	材料 MATERIAL: 電線銅 COPPER				参考図面 (CUSTOMER COPY) (REFERENCE ONLY)			
H					OBSOLETE	Y.O	N.Y	14APR17	H: FINISH ANNEAL TIN PL 焼付金 銅めっき				TE Connectivity			
G					Change Applicable Body	Y.O	N.Y	23JAN17	適合電線規格 (WIRE RANGE) 0.26~1.04 mm (AWG 22-16)							
F2					REVISED PER ECO-11-005030	RK	HMR	23MAR11	絶縁体 INSULATION DIA 表参照 SEE TABLE				形式 TYPE P.I.D.G フリッシュタイプ 3ワイヤードラッグ			
LTR					変更 REVISION RECORD	DR	CHK	DATE	一般公差 TOLERANCE EXCEPT AS NOTED ±0.4 ±1.0				分組 CLASS 4-1			
DR					2/6/13	DE			J A C-171508				REV J			
CHK					1/16/13	APP			9 型 端子 WIRE TERMINAL ASSEMBLY							

C-171508

単位: 寸法 DIMENSIONS IN MM DO NOT SCALE PRINT