



Our commitment. Your advantage.



• Products

- [By Type](#)

- [Connectors](#)
- [Electromechanical Components](#)
- [Electronic Modules](#)
- [Fiber Optics](#)
- [Filters](#)
- [Identification & Labeling](#)
- [Passive Components](#)
- [Power Sources](#)
- [RF & Microwave Products](#)
- [Tooling Products](#)
- [Touch Screen Displays](#)
- [Tubing, Molded and Harnessing Products](#)
- [Wire, Cable and Cable Assemblies](#)
- [List all product types...](#)

- [By Industry](#)

- [Aerospace & Defense Products](#)
- [Appliance](#)
- [Automotive](#)
- [Communications](#)
- [Computer & Consumer Electronics](#)
- [Industrial & Commercial](#)
- [Instrumentation & Medical](#)

- [By Brand](#)

- [A to Z](#)

- [Product News](#)

• Documentation

- [Find Documents & Drawings](#)

- [Find CAD Models](#)

- [SPICE/Electrical Models](#)

- [NAFTA Certificate of Origin](#)

- [White Papers](#)

• Resources

- [RoHS Compliance & Alternates](#)

- [Cross Reference Products](#)

- [Compare Multiple Products](#)

- [Check Distributor Inventory](#)

- [Find Authorized Distributors](#)

• My Account

- [Sign In](#)

- [Register](#)

• Customer Support

- [Support](#)

- [RoHS Support Center](#)

- [Glossary of Terms](#)

- [eBulletin Newsletter](#)

1-1520237-0 Product Details



Power Toggle Switches

Not EU RoHS or ELV Compliant

No Image Available

1-1520237-0



Product Highlights:

- Double Pole - Single Throw Configuration (Pole-Throw)
- Toggle Length = 17.07 mm
- Toggle Style = Baton
- Bushing Length = 11.91 mm
- Termination Type = Screw-In Terminal

[View all Features](#) | [Find Similar Products](#)

[Previous](#) [1](#) [2](#) [3](#) [4](#) [5](#) ... [20](#) [Next](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Compare Products](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [DIM'S FOR DBL. POLE TOOL HANDLE SW. FOR EUROPEAN USE](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version E)
- [3D Model](#) (IGES, Version E)
- [3D Model](#) (STEP, Version E)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Configuration (Pole-Throw) = Double Pole - Single Throw
- Termination Type = Screw-In Terminal

Configuration Related Features:

- Bushing Length (mm [in]) = 11.91 [0.469]

Electrical Characteristics:

- UL/CSA 125V Current Rating (Amps.) = 16
- UL/CSA 250V Current Rating (Amps.) = 8
- UL/CSA 125V Horse Power Rating (hp) = 1.00

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Housing Related Features:

- Toggle Length (mm [in]) = 17.07 [0.672]
- Toggle Style = Baton

Other:

- Brand = Alcoswitch

[Provide Website Feedback](#) | [Contact Customer Support](#)

[Home](#) | [Customer Support](#) | [Suppliers](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)

2008 Tyco Electronics Corporation All Rights Reserved