



881623-9 Product Details



881623-9

TE Internal Number: 881623-9

[Active](#)

FASTON Uninsulated Receptacles & Housings

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Terminal
- Terminal Type = Receptacle
- Mating Area Interface Dimensions = 4.75 x 0.51 mm
- Board Mount = No
- Receptacle Style = Straight

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Terminal
- Receptacle Style = Straight
- Insulation Support = Insulation Support
- Wire/Cable Type = Stranded
- Insertion Force = Normal/Low
- Finish = Tin

Mechanical Attachment:

- Board Mount = No

Termination Features:

- Crimp Type = F-Crimp

Dimensions:

- Mating Area Interface Dimensions (mm [in]) = 4.75 x 0.51 [.187 x .020]
- Insulation Diameter (mm [in]) = 2.00-3.30 [.079-.130]
- Length (mm [in]) = 15.10 [0.594]

Body Features:

- Wire Range (mm [AWG]) = 0.50-1.00² [20-17]
- Material = Brass
- With Dimple = With
- Stock Thickness (mm [in]) = 0.32 [0.0126]

Contact Features:

- Terminal Type = Receptacle

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- For Hermetic Header Tab = No
- Temperature Range (°C) = 110

Packaging Features:

- Packaging Method = Reel
- Packaging Quantity = 15,000

Other:

- Line = FASTON .187
- Brand = TE Connectivity

Feedback

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[AODA Accessibility Policy](#)
[AODA Multi-Year Accessibility Plan](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed



