

## Han 10Ex UL-HTE-M20



Image is for illustration purposes only. Please refer to product description.

Part number	19 36 510 1420
Specification	Han 10Ex UL-HTE-M20
HARTING eCatalogue	<a href="https://b2b.harting.com/19365101420">https://b2b.harting.com/19365101420</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han <sup>®</sup> Ex
Type of hood/housing	Hood

### Version

Size	10 B
Version	Top entry
Number of cable entries	1
Cable entry	1x M20
Locking type	Double locking lever
Field of application	Connectors for explosion hazardous environments
Details	for US purposes only
Details	ATTENTION! Only to be used with Han <sup>®</sup> Ex inserts!

### Technical characteristics

Limiting temperature	-20 ... +40 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 With cable gland

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 5015 (sky blue)



Pushing Performance  
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Commercial data

Packaging size	1
Net weight	310 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140181564
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors