

HC-STA-A04PT-BWS-HT-M20-PLRBK - Connector set



1424446

<https://www.phoenixcontact.com/us/products/1424446>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector set, number of positions: 4, material: PA, connection method: Push-in connection, connection cross section: AWG 26- 16

Commercial data

Item number	1424446
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF63
Product key	BF7AFX
GTIN	4055626372754
Weight per piece (including packing)	91.4 g
Weight per piece (excluding packing)	91.4 g
Customs tariff number	85366990
Country of origin	CN

HC-STA-A04PT-BWS-HT-M20-PLRBK - Connector set



1424446

<https://www.phoenixcontact.com/us/products/1424446>

Set consists of

HC-A04-I-PT-M - Contact insert

1585278

<https://www.phoenixcontact.com/us/products/1585278>



Contact insert, number of positions: 4+PE, size: D7, number of connections per position: 1, Pin, Push-in connection, 230 V/400 V, 10 A, 0.14 mm² ... 1.5 mm²

HC-A04-I-PT-F - Contact insert

1585281

<https://www.phoenixcontact.com/us/products/1585281>



Contact insert, number of positions: 4+PE, size: D7, number of connections per position: 1, Socket, Push-in connection, 230 V, 10 A, 0.14 mm² ... 1.5 mm²

HC-STA-A04PT-BWS-HT-M20-PLRBK - Connector set



1424446

<https://www.phoenixcontact.com/us/products/1424446>

HC-STA-D07-BWS-PL-BK - Housing

1419265

<https://www.phoenixcontact.com/us/products/1419265>



Panel mounting base D7, with single locking latch, material: PA, height: 25.5 mm, cable gland: none, Standard

HC-STA-D07-HHFS-1TGM20-PL-BK - Housing

1419255

<https://www.phoenixcontact.com/us/products/1419255>



Sleeve housing D7, for single locking latch, material: PA, cable outlets: 1, straight, 1x M20, height: 77.6 mm, cable gland: with, Standard

Technical data

Product properties

Product type	Connector set
Housing type	Complete housing
Application	Standard
Type	D7
Number of positions	4
No. of cable outlets	1
Protective cover	no

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Data management status

Article revision	02
------------------	----

Electrical properties

Rated voltage (III/3)	230 V (Conductor-PE)
	400 V (Conductor-Conductor)
Rated voltage for power contacts	230/400 V
Rated surge voltage	4 kV
Rated current	10 A

Connection data

Connection method	Push-in connection
Connection technology	Push-in connection
Conductor cross section	0.14 mm ² ... 1.5 mm ² (with ferrule)
	0.14 mm ² ... 1.5 mm ² (with ferrule)
Connection cross section AWG	26 ... 16 (with ferrule)
Stripping length of the individual wire	10 mm

Dimensions

Installation dimensions

Width of the assembly cutout	21 mm
Length of the assembly cutout	21 mm

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR, conductive
Housing material	PA
Contact material	Copper alloy
Contact surface material	Ag

HC-STA-A04PT-BWS-HT-M20-PLRBK - Connector set



1424446

<https://www.phoenixcontact.com/us/products/1424446>

Contact carrier material	PC
Locking latch material	PA

Cable/line

External cable diameter	4 mm ... 10 mm
Stripping length of the individual wire	10 mm


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
Enclosure rating (NEMA)	12 (UL 50e)
Impact strength	IK06
Ambient temperature (operation)	-40 °C ... 125 °C


Drawings

Schematic diagram




Pin assignment, connection side, pin left, socket right

Diagram




Derating diagram

Dimensional drawing



HC-A03
HC-A04
HC-D07
HC-D08
HC-Q05
HC-Q07
HC-Q12



HC-Q02
HC-Q03
HC-Q04

Mounting cutout

HC-STA-A04PT-BWS-HT-M20-PLRBK - Connector set



1424446

<https://www.phoenixcontact.com/us/products/1424446>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424446>

DNV

Approval ID: TAE000037S

HC-STA-A04PT-BWS-HT-M20-PLRBK - Connector set



1424446

<https://www.phoenixcontact.com/us/products/1424446>

Classifications

ECLASS

ECLASS-11.0	27440101
ECLASS-12.0	27440113
ECLASS-13.0	27440113

ETIM

ETIM 9.0	EC002636
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%