



P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



RECOMMENDED PCB LAYOUT																			
2 ● STANDARD DIRECTION ○ NO KINK 20 19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1 2P 3P 4P 5P 6P 7P 8P 9P 10P 11P 12P 13P 14P 15P 16P 17P 18P 19P 20P POS																			

YES	47.5 [1.870]	50.83[2.001]	52.5 [2.067]		20	NATURAL	2-2304185-0			
	45.0 [1.772]	48.33[1.903]	50.0 [1.968]		19		1-2304185-9			
	42.5 [1.673]	45.83[1.804]	47.5 [1.870]		18		1-2304185-8			
	40.0 [1.575]	43.33[1.706]	45.0 [1.772]		17		1-2304185-7			
	37.5 [1.476]	40.83[1.607]	42.5 [1.673]		16		1-2304185-6			
	35.0 [1.378]	38.33[1.510]	40.0 [1.575]		15		1-2304185-5			
	32.5 [1.280]	35.83[1.411]	37.5 [1.476]		14		1-2304185-4			
	30.0 [1.181]	33.33[1.312]	35.0 [1.378]		13		1-2304185-3			
	27.5 [1.083]	30.83[1.214]	32.5 [1.280]		12		6-2304185-2			
	25.0 [.984]	28.33[1.115]	30.0 [1.181]		11		1-2304185-1			
	22.5 [.886]	25.83[1.016]	27.5 [1.083]		10		1-2304185-0			
	20.0 [.787]	23.33[.919]	25.0 [.984]		9		2304185-9			
	17.5 [.689]	20.83[.820]	22.5 [.886]		8		2304185-8			
	15.0[.591]	18.33[.722]	20.0[.787]	2,3	7		2-2304185-7			
	15.0 [.591]	18.33[.722]	20.0 [.787]		7		2304185-7			
	12.5 [.492]	15.83[.623]	17.5 [.689]		6		2304185-6			
	10.0 [.395]	13.33[.525]	15.0 [.591]		5		2304185-5			
7.5 [.295]	10.83[.426]	12.5 [.492]		4	2304185-4					
5.0 [.197]	8.33[.328]	10.0 [.395]		3	2304185-3					
NO	2.5 [.098]	5.83[.229]	7.5 [.295]		2	GREEN	5-2304185-2			
NO					2	YELLOW	4-2304185-2			
YES					2	BLACK	3-2304185-2			
NO					2	BLUE	2-2304185-2			
NO					2	RED	1-2304185-2			
YES				2	NATURAL	2304185-2				
UL MARK	DIM C	DIM B	DIM A	OMIT PIN#	POS	COLOR	PART NO			
	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN OTTO CHEN 14JUL2016	TE Connectivity						
			CHK DANIEL 20JUL2016							
	DIMENSIONS: mm		APVD DANIEL 20JUL2016	NAME HEADER ASSEMBLY, VERTICAL, ECONOMY POWER 2.5mm.						
			PRODUCT SPEC 108-2418							
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.20 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH - -		APPLICATION SPEC 114-13315 WEIGHT - CUSTOMER DRAWING							
					SIZE A2	CAGE CODE -	DRAWING NO C=2304185	RESTRICTED TO -		
					SCALE N/A	SHEET 2	OF 2	REV A3		