

Protect cover Han-INOX for base panel



Image is for illustration purposes only. Please refer to product description.

Part number	19 44 310 5423
Specification	Protect cover Han-INOX for base panel
HARTING eCatalogue	https://b2b.harting.com/19443105423

Identification

Category	Accessories
Series of hoods/housings	Han-INOX®
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for cable to cable housing Metal With fixing cord (cable shoe)

Version

Size	10 B
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	199.2 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140132139
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors