

Coaxial Cable Connector 21_N-50-6-7/12-_N

Description

Straight cable jack

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz
Frequency range	DC to 18 GHz
Return loss	21.7 dB

Mechanical Data

Centre contact	plugged
Outer contact	clamped

Environmental Data

Operating temperature	-60 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Nickel Plating
Body	Brass	Nickel Plating
Other body part	Stainless Steel	
Insulator	PTFE (Polytetrafluoroethylene)	
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00321092
Assembly instruction	DOC-0000723577

Ordering Information

Single package	21_N-50-6-7/12-_NE
----------------	--------------------

Additional Information

Suitable cables	EACON_6C
-----------------	----------