

D-SUB sleeve housings - CUC-DST-GPME-S/DSSC25 - 1419719

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



D-SUB sleeve housings, Degree of protection: IP20, Material: ABS, metal-plated, Cable exit: straight, Size of housing: 3, Color: Bare metallic

Why buy this product

- ✓ Antimagnetic plastic housing
- Particularly suitable for D-SUB connectors with special contacts thanks to large interior



Key Commercial Data

Packing unit	1 STK
GTIN	4 055626 187891
GTIN	4055626187891

Technical data

Mechanical characteristics

External cable diameter	4 mm 12 mm
Cable exit	straight
Color	Bare metallic
Mounting type	Screw locking
Screw thread	4-40 UNC
Degree of protection	IP20
Туре	D-SUB 25
Size of housing	3
No. of cable outlets	1

Ambient conditions

Ambient temperature (operation)	-35 °C 95 °C

Material data



D-SUB sleeve housings - CUC-DST-GPME-S/DSSC25 - 1419719

Technical data

Material data

Flammability rating according to UL 94	V0
Housing material	ABS, metal-plated
Housing surface material	metal-plated

Standards and Regulations


Flammability rating according to UL 94	VO

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values


Drawings

Dimensional drawing



D-SUB sleeve housings

Schematic diagram



Phoenix Contact 2017 © - all rights reserved http://www.phoenixcontact.com

PHOENIX CONTACT GmbH & Co. KG Flachsmarktstr. 8 32825 Blomberg

Germany

Tel. +49 5235 300 Fax +49 5235 3 41200

http://www.phoenixcontact.com